

# **POWER TRANSFORMER** PC MOUNT: SPLIT PACK

# F24-100

## **Description:**

The F24-100 is a single primary and dual secondary, split bobbin design which operates with an input of 115V. The output voltage will be either 24.0V with a center-tap under a 0.1A load with the secondaries wired in series, or 12.0V under a 0.2A load with the secondaries wired in parallel. The split bobbin design eliminates the need for costly electrostatic shielding.

## **Electrical Specifications (@25C)**

- 1. Maximum Power: 2.5VA
- 2. Primary: 115V
- 3. Secondary: Series: 24.0V CT@ 0.1A
- Parallel: 12.0V @ 0.2A
- 4. Voltage Regulation: 25% TYP @ full load to no load
- 5. Temperature Rise: 25C TYP
- 6. Hipot tested 100% at 2500 VRMS

#### **Construction:**

Three flange bobbin construction with primaries and secondaries wound side by side for low capacitive coupling.

## Agency File:

UL: File E53148, UL 5085-2 (506), Class B General Purpose Transformer, cUL: File E53148, UL 5085-2 (506), Class B General Purpose Transformer, Canadian Use (CSA 22.2, No.66.2-06)


This model is also available in Class 2, UL 5085-3 (1585) version as F24-100-C2



Dimensions: Units in inches								ches.
Н	W	L	А	В	С	D	E	F
1.187	1.125	1.375	0.250	0.250	1.200	0.041	0.020	0.234

Weight: 0.25 lbs

#### Schematic:



**RoHS Compliance:** As of manufacturing date February 2005, all standard products meet the requirements of 2011/65/EU, known as the RoHS initiative.


As of April 7, 2008, UL standards 506 and 1585 will be migrated to UL 5085-2 and 5085-3, respectively.


\*Upon printing, this document is considered "uncontrolled". Please contact Triad Magnetics website for the most current version. For soldering and washing information please see http://www.triadmagnetics.com/faq.html

Web: www.TriadMagnetics.com Phone 951-277-0757 Fax 951-277-2757

460 Harley Knox Blvd. Perris, California 92571







Publish Date: June 7, 2016