

## HMC584LP5 / 584LP5E

v03.1210




# MMIC VCO w/ HALF FREQUENCY OUTPUT & DIVIDE-BY-4, 12.5 - 13.9 GHz

#### Typical Applications

Low noise MMIC VCO w/Half Frequency, Divide-by-4 Outputs for:

- Point to Point/Multipoint Radio
- Test Equipment & Industrial Controls
- SATCOM
- Military End-Use

#### **Functional Diagram**



#### **Features**

Dual Output: Fo = 12.5 - 13.9 GHzFo/2 = 6.25 - 6.95 GHz

Pout: +10 dBm

Phase Noise: -110 dBc/Hz @100 kHz Typ.

No External Resonator Needed

32 Lead 5x5mm SMT Package: 25mm²

#### **General Description**

The HMC584LP5 & HMC584LP5E are GaAs InGaP Heterojunction Bipolar Transistor (HBT) MMIC VCOs. The HMC584LP5 & HMC584LP5E integrate resonators, negative resistance devices, varactor diodes and feature half frequency and divide-by-4 outputs. The VCO's phase noise performance is excellent over temperature, shock, and process due to the oscillator's monolithic structure. Power output is +10 dBm typical from a +5V supply voltage. The prescaler and RF/2 functions can be disabled to conserve current if not required. The voltage controlled oscillator is packaged in a leadless QFN 5x5 mm surface mount package, and requires no external matching components.

## Electrical Specifications, $T_A = +25^{\circ}$ C, Vcc (Dig), Vcc (Amp), Vcc (RF) = +5V

Parameter		Min.	Тур.	Max.	Units
Frequency Range	Fo Fo/2		12.5 - 13.9 6.25 - 6.95		GHz GHz
Power Output	RFOUT/2 RFOUT/4	+7 +8 -9		+14 +14 -3	dBm dBm dBm
SSB Phase Noise @ 100 kHz Offset, Vtune= +5V @ RFOUT			-110		dBc/Hz
Tune Voltage	Vtune	2		12	V
Supply Current	Icc(Dig) + Icc(Amp) + Icc(RF)	290	330	380	mA
Tune Port Leakage Current (Vtune= 12V)				10	μA
Output Return Loss			2		dB
Harmonics/Subharmonics	1/2 3/2 2nd 3rd		28 34 29 40		dBc dBc dBc dBc
Pulling (into a 2.0:1 VSWR)			3		MHz pp
Pushing @ Vtune= 5V			20		MHz/V
Frequency Drift Rate			1.5		MHz/°C

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.

## **HMC584\* PRODUCT PAGE QUICK LINKS**

Last Content Update: 02/23/2017

### COMPARABLE PARTS 🖳

View a parametric search of comparable parts.

### **EVALUATION KITS**

• HMC584LP5 Evaluation Board.

### **DOCUMENTATION**

#### **Data Sheet**

• HMC584 Data Sheet

#### REFERENCE MATERIALS -

#### **Quality Documentation**

- Package/Assembly Qualification Test Report: 32L 5x5mm QFN Package (QTR: 10009 REV: 05)
- Package/Assembly Qualification Test Report: LP3, LP4, LP5 & LP5G (QTR: 2014-00145)
- Package/Assembly Qualification Test Report: Plastic Encapsulated QFN (QTR: 05006 REV: 02)
- Semiconductor Qualification Test Report: GaAs HBT-A (QTR: 2013-00228)

## DESIGN RESOURCES 🖵

- HMC584 Material Declaration
- PCN-PDN Information
- · Quality And Reliability
- · Symbols and Footprints

#### **DISCUSSIONS**

View all HMC584 EngineerZone Discussions.

### SAMPLE AND BUY 🖵

Visit the product page to see pricing options.

### **TECHNICAL SUPPORT**

Submit a technical question or find your regional support number.

#### DOCUMENT FEEDBACK 🖳

Submit feedback for this data sheet.

This page is dynamically generated by Analog Devices, Inc., and inserted into this data sheet. A dynamic change to the content on this page will not trigger a change to either the revision number or the content of the product data sheet. This dynamic page may be frequently modified.




v03.1210




# MMIC VCO w/ HALF FREQUENCY OUTPUT & DIVIDE-BY-4, 12.5 - 13.9 GHz


#### Frequency vs. Tuning Voltage, Vcc = +5V




#### Frequency vs. Tuning Voltage, T= 25°C




#### Sensitivity vs. Tuning Voltage, Vcc = +5V




Output Power vs. Tuning Voltage, Vcc = +5V



#### SSB Phase Noise vs. Tuning Voltage



#### SSB Phase Noise @ Vtune = +5V









# MMIC VCO w/ HALF FREQUENCY OUTPUT & DIVIDE-BY-4, 12.5 - 13.9 GHz

# RFOUT/2 Frequency vs. Tuning Voltage, Vcc = +5V




v03.1210


# RFOUT/2 Output Power vs. Tuning Voltage, Vcc = +5V



# Divide-by-4 Frequency vs. Tuning Voltage, Vcc = +5V



# Divide-by-4 Output Power vs. Tuning Voltage, Vcc = +5V



#### **Absolute Maximum Ratings**

Vcc(Dig), Vcc(Amp), Vcc(RF)	+5.5 Vdc
Vtune	0 to +15V
Junction Temperature	135 °C
Continuous Pdiss (T=85 °C) (derate 43.5 mW/C above 85 °C	2.17 W
Thermal Resistance (junction to ground paddle)	23 °C/W
Storage Temperature	-65 to +150 °C
Operating Temperature	-40 to +85 °C
ESD Sensitivity (HBM)	Class 1A

#### Typical Supply Current vs. Vcc

Vcc (V)	Icc (mA)
4.75	300
5.00	330
5.25	360

Note: VCO will operate over full voltage range shown above.



ELECTROSTATIC SENSITIVE DEVICE OBSERVE HANDLING PRECAUTIONS




v03.1210



# MMIC VCO w/ HALF FREQUENCY OUTPUT & DIVIDE-BY-4, 12.5 - 13.9 GHz

#### **Outline Drawing**



SEATING

-C-

- 1. LEADFRAME MATERIAL: COPPER ALLOY
- 2. DIMENSIONS ARE IN INCHES [MILLIMETERS]
- 3. LEAD SPACING TOLERANCE IS NON-CUMULATIVE.
- 4. PAD BURR LENGTH SHALL BE 0.15mm MAXIMUM. PAD BURR HEIGHT SHALL BE 0.05mm MAXIMUM.
- 5. PACKAGE WARP SHALL NOT EXCEED 0.05mm.
- 6. ALL GROUND LEADS AND GROUND PADDLE MUST BE SOLDERED TO PCB RF GROUND.
- 7. REFER TO HITTITE APPLICATION NOTE FOR SUGGESTED LAND PATTERN.

## Package Information

☐ .003[0.08] C

Part Number	Package Body Material	Lead Finish	MSL Rating	Package Marking [3]
HMC584LP5	Low Stress Injection Molded Plastic	Sn/Pb Solder	MSL3 [1]	H584 XXXX
HMC584LP5E	RoHS-compliant Low Stress Injection Molded Plastic	100% matte Sn	MSL3 [2]	H584 XXXX

- [1] Max peak reflow temperature of 235  $^{\circ}\text{C}$
- [2] Max peak reflow temperature of 260  $^{\circ}\text{C}$
- [3] 4-Digit lot number XXXX

#### **Pin Descriptions**

Pin Number	Function	Description	Interface Schematic
1 - 3, 8 - 10, 13 - 18, 20, 22 - 28, 30 - 32	N/C	No Connection. These pins may be connected to RF/ DC ground. Performance will not be affected.	
4	RFOUT/4	Divide-by-4 output. DC block required.	5V ORFOUT/4
6	Vcc (Dig)	Supply voltage for prescaler. If prescaler is not required, this pin may be left open to conserve approximately 65 mA of current.	Vcc(Dig)






# MMIC VCO w/ HALF FREQUENCY OUTPUT & DIVIDE-BY-4, 12.5 - 13.9 GHz

#### **Pin Descriptions**

Pin Number	Function	Description	Interface Schematic
7	Vcc (Amp)	Supply voltage, for RFOUT/2 output. If RFOUT/2 is not required, this pin may be left open to conserve approximately 30 mA of current.	Vcc(Amp)  14pF
12	RFOUT/2	Half frequency output (AC coupled).	PFOUT/2
19	RF OUT	RF output (AC coupled).	RFOUT
21	Vcc (RF)	Supply Voltage, +5V	Vec(RF)  14pF
29	VTUNE	Control voltage and modulation input. Modulation bandwidth dependent on drive source impedance. See "Determining the FM Bandwidth of a Wideband Varactor Tuned VCO" application note.	3nH VTUNE 0
5, 11, Paddle	GND	Package bottom has an exposed metal paddle that must be connected to RF/DC ground.	- GND

v03.1210

### **Typical Application Circuit**








# MMIC VCO w/ HALF FREQUENCY OUTPUT & DIVIDE-BY-4, 12.5 - 13.9 GHz

#### **Evaluation PCB**



#### List of Materials for Evaluation PCB 110227 [1]

Item	Description
J1 - J4	PCB Mount SMA RF Connector
J5 - J6	2 mm DC Header
C1 - C3	100 pF Capacitor, 0402 Pkg.
C4	1,000 pF Capacitor, 0402 Pkg.
C5 - C7	2.2 µF Tantalum Capacitor
U1	HMC584LP5 / HMC584LP5E VCO
PCB [2]	110225 Eval Board

[1] Reference this number when ordering complete evaluation PCB

[2] Circuit Board Material: Rogers 4350

The circuit board used in the application should use RF circuit design techniques. Signal lines should have 50 Ohm impedance while the package ground leads and backside ground paddle should be connected directly to the ground plane similar to that shown. A sufficient number of via holes should be used to connect the top and bottom ground planes. The evaluation circuit board shown is available from Hittite upon request.