

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0923211610](#)  
**Status:** **Active**  
**Overview:** QF-50™  
**Description:** 1.27mm Pitch QF-50™ Cable Assembly, QF-50™-to-QF-50™, 16 Circuits, 0.10m Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

|                        |                        |
|------------------------|------------------------|
| Product Family         | Cable Assemblies       |
| Series                 | <a href="#">92321</a>  |
| Assembly Configuration | Dual Ended Connectors  |
| Connector to Connector | QF-50™-to-QF-50™       |
| Overview               | <a href="#">QF-50™</a> |
| Product Name           | QF-50™                 |
| UPC                    | 800756075945           |


**Physical**

|                          |               |
|--------------------------|---------------|
| Cable Length             | 0.10m         |
| Circuits (Loaded)        | 16            |
| Gender                   | Female-Female |
| Net Weight               | 6.540/g       |
| Packaging Type           | Bag           |
| Pitch - Mating Interface | 1.27mm        |
| Single Ended             | No            |
| Wire/Cable Type          | Ribbon Cable  |

**Material Info**

**Reference - Drawing Numbers**

|               |              |
|---------------|--------------|
| Sales Drawing | SD-92321-001 |
|---------------|--------------|



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/01/2017 (12  
January 2017)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[92321 Series](#)