G3VM-21UR

MOS FET Relays VSON, Low-output-capacitance and Low-ON-resistance Type (with Low C × R)

World's smallest * class New VSON Package with Low Output Capacitance and Low ON Resistance

* As of November 2016 Survey by OMRON.

• Load voltage: 20 V

• G3VM-21UR10: Low C \times R = 2.4 pF· Ω , Coff (standard) = 0.8 pF,

Ron (standard) = 3 Ω

• G3VM-21UR1: Low C \times R = 4 pF $\cdot\Omega$, Coff (standard) = 5 pF,

Ron (standard) = 0.8 Ω

• G3VM-21UR11: Low C \times R = 7.2 pF· Ω , Coff (standard) = 40 pF,

Ron (standard) = 0.18 Ω

• High Ambient operating temperature: -40°C to +110°C

RoHS Compliant



Note: The actual product is marked differently from the image shown here.


■Application Examples

- Semiconductor test equipment
- Communication equipment
- Test & measurement equipment
- Data loggers

■Package (Unit: mm, Average)

■Model Number Legend

VSON 4-pin



Note: The actual product is marked differently from the image shown here.

1. Load Voltage

2. Contact form

3. Package

2: 20 V

1: 1a (SPST-NO)

U: VSON 4-pin

4. Additional functions 5. Other informations

R: Low On-resistance

When specifications overlap, serial code

is added in the recorded order.

■Ordering Information

Package	Contact form	Terminals	Load voltage (peak value) *	Continuous load current (peak value) *	Tape cut packaging		Tape packaging	
					Model	Minimum package quantity	Model	Minimum package quantity
		Surface-mounting Terminals	20 V	200 mA	G3VM-21UR10	1 pc.	G3VM-21UR10(TR05)	500 pcs.
VSON4	1a (SPST-NO)			450 mA	G3VM-21UR1		G3VM-21UR1(TR05)	
				1,000 mA	G3VM-21UR11		G3VM-21UR11(TR05)	

Note: To order tape packaging for Relays with surface-mounting terminals, add "(TR05)" to the end of the model number. Tape-cut VSONs are packaged without humidity resistance. Use manual soldering to mount them. Refer to common precautions.

* The AC peak and DC value are given for the load voltage and continuous load current.

■Absolute Maximum Ratings (Ta = 25°C)


	Item	Symbol	G3VM-21UR10	G3VM-21UR1	G3VM-21UR11	Unit	Measurement conditions	
LED forward current		lF		30	mA			
Ħ	LED forward current reduction rate	ΔIF/°C		-0.3	mA/°C	Ta≥25°C		
Inp	LED reverse voltage	VR		5	V			
	Connection temperature	TJ	125			°C		
Load voltage (AC peak/DC)		Voff	20			V		
Output	Continuous load current (AC peak/DC)	lo	200	450	1,000	mA		
	ON current reduction rate	Δlo/°C	-2	-4.5	-10	mA/°C	Ta≥25°C	
	Pulse ON current	lop	0.6	1.3	3	Α	t=100 ms, Duty=1/10	
	Connection temperature	TJ	125					
	Dielectric strength between I/O (See note 1.) (See note 2.)		500			Vrms	AC for 1 min	
Ambient operating temperature		Ta	-40 to +110			°C	With no icing or condensation	
Ambient storage temperature		Tstg	-40 to +125			°C	with no long of condensation	
So	ldering temperature	-	260			°C	10 s	

Note: 1. The dielectric strength between the input and output was checked by applying voltage between all pins as a group on the LED side and all pins as a group on

■Electrical Characteristics (Ta = 25°C)

	Item			G3VM-21UR10	G3VM-21UR1	G3VM-21UR11	Unit	Measurement conditions	
		VF	Minimum	1.1			V	IF=10 mA	
	LED forward voltage		Typical	1.27					
			Maximum	1.4					
Input	Reverse current	lr	Maximum	10			μΑ	V _R =5 V	
르	Capacitance between terminals	Ст	Typical	30			pF	V=0, f=1 MHz	
	Trigger LED forward current	lft	Typical	1	0.6	-	mA	lo=100 mA	
			Maximum		3		IIIA		
	Release LED forward current	IFC	Minimum	0.1		mA	Ioff=10 μA		
	Maximum resistance with output ON	Ron	Typical	3	0.8	0.18	Ω	IF=5 mA, t<1 s,	
			Maximum	5	1.2	0.22		lo=Continuous load current ratings	
Output	Current leakage when the relay is open	ILEAK	Maximum	1			nA	Voff=20 V	
	Capacitance between terminals	Coff	Typical	0.8	5	40	pF	V=0, f=100 MHz, t<1 s	
			Maximum	1.1	12	-		V=0, I=100 MHZ, I<1 S	
Ca	pacitance between I/O terminals	C _{I-O}	Typical	1 0.4			pF	f=1 MHz, Vs=0 V	
	Insulation resistance between I/O terminals		Typical	108			10 ⁸ ΜΩ V _{I-O} =500 V		Vi-o=500 VDC, RoH≤60%
т	Turn-ON time		Typical	0.05	0.17	-			
Tu			Maximum	0.2	0.4 2		me	IF=5 mA, RL=200 Ω ,	
Т	Turn-OFF time		Typical	0.02 –		ms	V _{DD} =10 V (See note 2.)		
Tu			Maximum	0.2	0.4	1			

Note: 3. Turn-ON and Turn-OFF Times



■Recommended Operating Conditions

For usage with high reliability, Recommended Operation Conditions is a measure that takes into account the derating of Absolute Maximum Ratings and Electrical Characteristics.


Each item on this list is an independent condition, so it is not simultaneously satisfy several conditions.

Item	Symbol		G3VM-21UR10	G3VM-21UR1	G3VM-21UR11	Unit
Load voltage (AC peak/DC)	V _{DD}	Maximum	16		V	
		Minimum		mA		
Operating LED forward current	lF	Typical				
		Maximum	20			
Continuous load current (AC peak/DC)	lo	Maximum	200	450	1,000	
Ambient operating temperature	Та	Minimum	-20			- °C
Ambient operating temperature	Ια	Maximum	85			


^{2.} Dielectric strength between I/O 500Vrms is applied from production in December 2016. (Before changes are 300Vrms.)

■Engineering Data


LED forward current vs. Ambient temperature




Continuous load current vs. On-state voltage




Trigger LED forward current vs. Ambient temperature




Continuous load current vs. Ambient temperature




●On-state resistance vs. Ambient temperature G3VM-21UR1/21UR11




●Turn ON, Turn OFF time vs. LED forward current G3VM-21UR10/21UR1




LED forward current vs. LED forward voltage



G3VM-21UR10




G3VM-21UR11




■Engineering Data


●Turn ON, Turn OFF time vs. Ambient temperature G3VM-21UR10/21UR1




G3VM-21UR11




Current leakage vs. Load voltage



Current leakage vs. Ambient temperature



Output terminal capacitance vs. Load voltage



■Appearance / Terminal Arrangement / Internal Connections

Appearance

VSON (Very Small Outline Non-leaded)


VSON 4-pin



* Actual model name marking for each model

each model					
Model	Marking				
G3VM-21UR10	2UA				
G3VM-21UR1	2U1				
G3VM-21UR11	2UB				

Terminal Arrangement/Internal Connections (Top View)



Note: 1. The actual product is marked differently from the image shown here.


Note: 2. "G3VM" does not appear in the model number on the Relay.

■Dimensions (Unit: mm)

Surface-mounting Terminals


Weight: 0.01 g





Actual Mounting Pad Dimensions

(Recommended Value, Top View)



Unless otherwise specified, the dimensional tolerance is \pm 0.1 mm.

Note: The actual product is marked differently from the image shown here.

■Safety Precautions

• Refer to the Common Precautions for All MOS FET Relays for precautions that apply to all MOS FET Relays.

Application examples provided in this document are for reference only. In actual applications, confirm equipment functions and safety before using the product.
Consult your OMRON representative before using the product under conditions which are not described in the manual or applying the product to nuclear control systems, railroad systems, aviation systems, excitous, combustion systems, medical equipment, amusement machines, safety equipment, and other systems or equipment that may have a serious influence on lives and property if used improperly. Make sure that the ratings and performance characteristics of the product provide a margin of safety for the system or equipment, and be sure to provide the system or equipment with double safety mechanisms.

Contact: www.omron.com/ecb

Note: Do not use this document to operate the Unit.

OMRON Corporation

Electronic and Mechanical Components Company

Cat. No. K267-E1-04 0117(0814)(O)