## Panasonic Conductive Polymer Aluminum Solid Capacitors

## **Radial Lead Type**

Series : **SEPG** 

**OS**-CON




## Features

• High ripple current (5800 mA.r.m.s.)

• RoHS compliance, Halogen free

Specifications					
Size code	C10				
Category temperature range	–55 °C to +105 °C				
Rated voltage range	16 V.DC				
Rated capacitance range	270 µF				
Capacitance tolerance	±20 % (120 Hz / + 20 °C)				
Leakage current	Please see the attached characteristics list				
Dissipation factor (tan $\delta$ )	Please see the attached characteristics list				
Endurance	+105 °C, 5000 h, rated voltage applied				
	Capacitance change	Within ±20 % of the initial value			
	tan $\delta$	≤ 150 % of the initial limit			
	DC leakage current	Within the initial limit			
Damp heat (Steady State)	+60 °C, 90 % to 95 %, 1000 h, No-applied voltage				
	Capacitance change	Within ±20 % of the initial value			
	tan $\delta$	≤ 150 % of the initial limit			
	DC leakage current	Within the initial limit (after voltage processing)			



## Specifications Case size (mm) Rated Rated Size Ripple\* voltage Series capacitance ESR\*2 LC \*4 Part number tan $\delta^{*^3}$ code φD L current (V.DC) (µF) $(m\Omega max.)$ (µA) (mAr.m.s.) SEPG 270 6.3 10.0 C10 5800 0.12 864 16SEPG270M 16 8

\*1 Ripple current (100 kHz/ +105 °C ), \*2 ESR (100 kHz/+20 °C) \*3 tan δ (120 Hz/+20 °C) \*4 After 2 minutes

◆ Please refer to each page in this catarog for "Flow conditions" and "Taping specifications"

Frequency correction factor for ripple current						
Frequency	120 Hz ≦ f < 1 kHz	1 kHz ≦ f < 10 kHz	10 kHz ≦ f < 100 kHz	100 kHz ≦ f < 500 kHz		
Coefficient	0.05	0.3	0.7	1		

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use Should a safety concern arise regarding this product, please be sure to contact us immediately.