

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0901310770

Status:

Active

Overview:

C-Grid III™

Description:

2.54mm Pitch C-Grid III™ Header, Dual Row, Vertical, 20 Circuits, 0.38µm Gold (Au) Selective Plating

Documents:

3D Model

Drawing (PDF)

Packaging Specification PK-90131-0001 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Overview

Product Name

UPC

PCB Headers

90131

Signal, Wire-to-Board

C-Grid III™

C-Grid III™

800753538863

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

First Mate / Last Break

Glow-Wire Compliant

Guide to Mating Part

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Retention

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Polarized to PCB

Shrouded

Stackable

Temperature Range - Operating

Termination Interface: Style

Yes

20

20

Black

No

No

No

None

None

Brass

Gold

Tin

Polyester

1.233/g

2

Vertical

2.90mm

No

None

Tray

2.54mm

2.54mm

No

No

No

Yes

-55°C to +125°C

Through Hole

Electrical

Current - Maximum per Contact

Voltage - Maximum

3.0A

350V


Solder Process Data

Lead-freeProcess Capability

WAVE

Material Info

Reference - Drawing Numbers



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per

-ED/01/2017 (12

January 2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product

environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any

non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

90131 Series

This document was generated on 02/28/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION