

VLS3P040R1

TeSys VLS - Body switch disconnecter - 3 poles - 40 A - on DIN rail

Product availability : Stock - Normally stocked in distribution facility



Main

Range	TeSys
Product name	TeSys VARIO LS
Device short name	VLS3P
Product or component type	Switch body
Performance level	High performance
Poles description	3P
Contacts type and composition	3 NO
Network type	AC
Network frequency	50/60 Hz
Control type	Rotary handle
Rotary handle mounting style	Direct
Handle colour	Black
Handle front plate colour	Grey
Suitability for isolation	Yes

Complementary

Rotary handle padlocking	1 padlock 4 mm
Marking	0 - 1
Mounting support	Back mounting on DIN rail
Fixing mode	By clips back
System Voltage	690 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
[Ith] conventional free air thermal current	40 A at 55 °C
[Ithe] conventional enclosed thermal current	40 A
[Ie] rated operational current	25 A (AC-23A) at 500 V 25 A (AC-23A) at 690 V

	40 A (AC-21A) at 400 V 40 A (AC-21A) at 500 V 40 A (AC-21A) at 690 V 40 A (AC-22A) at 400 V 40 A (AC-22A) at 500 V 40 A (AC-22A) at 690 V 40 A (AC-23A) at 400 V 40 A at 600 V according to UL 508
Rated operational power in W	22 kW at 690 V (AC-23A) 18.5 kW at 500 V (AC-23A) 18.5 kW at 400 V (AC-23A)
Intermittent duty class	Class 120 - 60 %
Making capacity	60 A at 690 V (AC-21A) 120 A at 690 V (AC-22A) 400 A at 690 V (AC-23A)
[Icm] rated short-circuit making capacity	1128 A at 690 V
[Icw] rated short-time withstand current	800 A at 690 V during 1 s
Rated conditional short-circuit current	50 kA at 400 V - associated fuse 40 A gG
Breaking capacity	60 A at 690 V AC-21A 120 A at 690 V AC-22A 320 A at 690 V AC-23A
Device composition	Handle Switch
Mechanical durability	100000 cycles
Electrical durability	100000 cycles AC-21A
Connections - terminals	Power circuit : screw clamp terminals cable 16 mm ² - cable stiffness: flexible - without cable end Power circuit: screw clamp terminals cable 0.02 in ² (10 mm ²) - cable stiffness: solid
Tightening torque	Power circuit : 1.8...2 N.m - on screw clamp terminals
Height	2.95 in (75 mm)
Width	1.42 in (36 mm)
Depth	3.07 in (78 mm)
Product weight	0.3 lb(US) (0.135 kg)
Colour	Grey

Environment

Standards	IEC 60947-3 UL 508 CSA C22.2 No 14
Product certifications	GL
IP degree of protection	IP20 conforming to IEC 60529
Mechanical robustness	Vibrations 2...100 Hz Fc 0.7 g IEC 60068-2-6 Shocks 11 ms Ea 15 gn IEC 60068-2-27
Ambient air temperature for operation	-13...131 °F (-25...55 °C)
Fire resistance	1760 °F (960 °C) conforming to IEC 60695-2-11

Ordering and shipping details

Category	21734 - TESYS VLS DISCONNECT SWITCHES
Discount Schedule	CP1
GTIN	00785901560463
Nbr. of units in pkg.	1
Package weight(Lbs)	0.38
Returnability	Y
Country of origin	IT