

111-01670



Article Number: 111-01670

Description: High-Temp. Cable Tie, 5.9" Long, 100lb Tensile Strength, PAEK, Beige, 100/pkg

| | | |
|-----------------------------------|-----------------------|--|
| Base Data | Local Order Number | 111-01670 |
| | Type | PAT100R |
| | Color | Beige (BGE) |
| | Features and benefits | <ul style="list-style-type: none"> • Very high heat resistance up to 200°C (392°F). • PAEK material has 2X higher tensile strength than nylon. • PAEK material offers very good chemical resistance against hydrocarbons. |
| | Quantity Per | bag |
| | Product Description | HellermannTyton PAEK cable ties offer very high temperature resistance for use in demanding applications such as in engine compartments, near exhaust, and in enclosed industrial cabinets. The PAEK ties are inside serrated and feature a high performance design that, along with the material, offer extremely high tensile strength for tough applications. |
| | Short Description | High-Temp. Cable Tie, 5.9" Long, 100lb Tensile Strength, PAEK, Beige, 100/pkg |
| | Product Dimensions | Minimum Tensile Strength (Imperial) |
| Minimum Tensile Strength (Metric) | | 445.0N |
| Length L (Imperial) | | 5.9" |
| Length L (Metric) | | 149.9mm |
| Width W (Imperial) | | 0.33" |
| Width W (Metric) | | 8.0mm |
| Bundle Diameter Min. (Imperial) | | 0.06" |
| Bundle Diameter Min. (Metric) | | 1.5mm |
| Bundle Diameter Max. (Imperial) | | 1.38" |
| Bundle Diameter Max. (Metric) | | 35.0mm |
| Material and Specifications | Material | Polyaryletherketone (PAEK) |
| | Material Shortcut | PAEK |
| | | |

111-01670



| | | |
|-----------------------------|-----------------------------|-----------------------------------|
| Material and Specifications | Flammability | UL 94 V0 |
| | Operating Temperature | -67°F to +392°F (-55°C to +200°C) |
| | ROHS Compliant | Yes |
| Logistic and Packaging | | |
| | Package Quantity (Imperial) | 100 |
| | Package Quantity (Metric) | 100 |
| | Customs Number(Schedule B) | 3926909987 |