



**GREENLEE.**  
A Textron Company

MADE FOR THE TRADE!™

FISHTAPE,FIBERGLASS-.187"X250' IN REEL

Fiberglass Fish Tape 250' × 3/16 (76.2 m × 4.8 mm)IN  
REEL STAND



Image  
Unavailable

|     |         |
|-----|---------|
| MPN | 542-250 |
|-----|---------|

Cat No: 50357476

UPC No: 783310357476

#### Description

---

- Non-conductive fiberglass tape with patented low-friction coating for faster and easier fishing
- Perfect for fishing in conduit with wire or cable present
- Advanced comfort handle grip reduces fatigue
- Superior rapid tape pay-out and rewind
- Smaller Fish Eye with offset bend for improved fishing ability
- Improved low profile tip for easy fishing through all sizes of conduit
- Viewing Port gives visibility to remaining tape and ability to remove jobsite debris quickly
- Rugged case design improves drop impact capability
- Flared case with Grip Ridges for no slip handling
- Available in 50 FT (15.2 m), 100 FT (30.5 m) and 250 FT(76.2 m) lengths
- Replaceable tips
- Exclusive, unique, lightweight reel for easy positive feed out and rewind
- Excellent for installation of telecommunications and data communication cables in overhead plenums, above suspended ceilings and under floors
- Fiberglass fish tape is the fastest manual fish tape available. It is intended for fishing only. Rope or line is recommended for pulling.

## Specifications

---

- Accessory : 35919 1/8 IN (3 MM) Pulling Eye, 35930 3/16 IN (4.7 MM) Pulling Eye
- Application : For Installation Of Telecommunications And Data Communication Cables In Overhead Plenums, Above Suspended Ceilings And Under Floors And For Fishing In Conduit With Wire Or Cable Present
- Diameter : 3/16 IN (4.700 MM)
- Length : 250.000 FT (76.200 M)
- Material : Fiberglass
- Reel Type : Lightweight
- Replacement Part :
  - 05158 Replacement Fiberglass Tape - 250 FT X 3/16 IN (NO CASE)
  - 10565 Pulling Eye Repair Kit For 11/64 IN (4.3 MM) Diameter Fish Tapes (Includes: Pulling Eye And Adhesive)
  - 35750 Accessory Kit For 3/16 IN (4.78 MM) Fish Tapes (Includes Flexible Pulling Leader, Flexible Pushing Leader, Pulling Eye, Splice Ferrule And Threaded Ferrule)
- Sub Brand : MagnumPRO
- Tensile Strength : 400.000 LB (1.700 KN) Maximum Design Strength
- Type : Non Conductive
- Weight : 17.000 LB (7.700 KG)
- Width : 3/16 IN (4.800 MM)