



## HY435/12 FV

12 pole red-brown polyamide PA6.6, with 25% glass fibre reinforced pillar terminal block 14.5mm pitch 76a 450v



### SPECIFICATION

<b>Number of Poles</b>	12
<b>Terminal Material</b>	OT58 nickel plated
<b>Body Material</b>	Polyamide PA6.6, with 25% glass fibre reinforced
<b>Colour</b>	Red-brown
<b>Glow Wire Resistance Test Temp</b>	GWT750°C in 2 sec (EN60695-2-11)
<b>Max Conductor Size (Sq mm)</b>	16
<b>Max Current (A)</b>	76
<b>Max Voltage (V)</b>	450
<b>Working Temperature</b>	150
<b>Pitch (mm)</b>	14.5
<b>Height (mm)</b>	25
<b>Width (mm)</b>	32.2
<b>Length (mm)</b>	173.5
<b>Diameter (mm)</b>	4.2
<b>Terminal Screw Material</b>	White zinc plated steel