


Aluminum Electrolytic, 85C, ALS70, 0.062 F, 20%, 25 V, -40/+85C



Dimensions	
D	36mm +/-1mm
L	82mm +/-2mm
T	7.14mm +/-0.5mm
S	12.8mm +/-0.5mm
DT	8mm +/-0.5mm
LT	87.5mm +/-1mm
TD	10mm MIN
V	8mm NOM

Packaging Specifications	
Weight:	115 g
Sleeving:	Yes
Packaging:	T&R

General Information	
Dielectric:	Aluminum Electrolytic
Series:	ALS70
Description:	Screw Terminal, Aluminum Electrolytic
RoHS:	Yes
Notes:	Dimensions D And L Include Sleeving. MS (MxH) = M8x 12

Specifications	
Capacitance:	0.062 F
Capacitance Tolerance:	20%
Voltage DC:	25 VDC, 28.75 VDC (Surge)
Temperature Range:	-40/+85C
Rated Temperature:	85C
Life:	2000 Hrs
Resistance:	25 mOhms (100Hz 20C), 23 mOhms (10kHz 20C)
Current:	13.5 Amps (100Hz 85C), 15.1 Amps (10 kHz 85C)
Leakage:	6000 uAmps (5min 20C)