


Aluminum Electrolytic, 105C, ALS80, 7500 uF, 20%, 350 V, -40/+105C



Dimensions

D	77mm +/-1mm
L	5mm +/-2mm
T	5.5mm +/-0.5mm
S	31.8mm +/-0.5mm
DT	13mm +/-0.5mm
LT	110.5mm +/-1mm
TD	10mm MIN
V	19mm NOM
Z	10mm NOM

Packaging Specifications

Weight:	690 g
Sleaving:	Yes
Packaging:	T&R

General Information

Dielectric:	Aluminum Electrolytic
Series:	ALS80
Description:	Screw Terminal, Aluminum Electrolytic
RoHS:	Yes
Notes:	Dimensions D And L Include Sleaving. MS (MxH) = M12x 16

Specifications

Capacitance:	7500 uF
Capacitance Tolerance:	20%
Voltage DC:	350 VDC, 385 VDC (Surge), 500 VDC (Surge)
Temperature Range:	-40/+105C
Rated Temperature:	105C
Life:	2000 Hrs
Resistance:	29 mOhms (100Hz 20C), 19 mOhms (10kHz 20C)
Current:	14 Amps (100Hz 105C), 19.9 Amps (10 kHz 105C)
Leakage:	6000 uAmps (5min 20C)