

SG-P11-050-005-12-HH-782X-00000

PLANETARY GEARBOXES


SG 050

$i=005$


$\varphi=12'$

MADE
IN
ITALY

IP64




Dimensions (Units:mm)



1.1
Kg

MODEL	Rated output torque [Nm]	Maximum acceleration output torque [Nm]	Emergency step output torque [Nm]	Backlash [arcmin]	Nominal input speed [min ⁻¹]	Maximum momentary input speed [min ⁻¹]	Torsional stiffness [Nm/arcmin]	Maximum radial force applying on output shaft [N]	Maximum axial force applying on output shaft [N]	Gear efficiency [%]	Gear moment of inertia [Kg·m ²]
SG-P11-050-005-12-HH-782X-00000	12	20	30	12'	3500	5000	0.9	500	600	97	0.05x10 ⁻⁴

Suggested motors



103-H7823 SERIES



MOUNTING OPERATION MODE: ■ Tightening torque M=5 Nm ■ Locking bolt M4 ■ R.T.A. Quality Control