

TT Dial

TT Dial Measuring Torque Screwdrivers

Torque range from 0.1 to 5 N.m

The Gedore Torque range of Dial Measuring Torque Screwdrivers is designed for torque evaluation and torque verification, in order to ensure process conformity, product safety and absolute reliability. These low

cost and versatile tools provide accuracy, reliability and economy in a wide range of Maintenance and Repair, Quality Control, R & D and Assembly operations in any engineering or manufacturing environment.



TT 100 FH

T-Bar is not included with the TT Screwdriver Range

INDUSTRY SECTORS

Maintenance & Repair



Aerospace



Military



Utilities

Quality Control



Aerospace



Automotive



Packaging

Versatile Torque Measuring Screwdrivers for any manufacturing environment

Absolute accuracy. Unique torsion bar mechanism to ensure total precision

Dual scale. Dial provides efficient measurement in Metric and Imperial torque units in both directions, delivering flexibility and minimising tool investment


Ease of use. Lightweight materials. Tools can be used by operators at any skill level

Long tool life. High quality, robust construction: stainless steel shaft, attractive coloured aluminium handle and sturdy dial

Measure Process Conformity. Unique memory function enables these tools to carry out the Just Move and Break Loose Quality Auditing Tests

No risk of tool damage. Overload Protection System with unique positive contact mechanism

Operational versatility. Torque can be measured as it is applied (Track mode) or when the maximum torque value has been recorded (Peak mode)



Additional features

Calibration Service enables tools to be kept accurate and up to date.
See page 82

Two year warranty provides additional peace of mind

Range of accessories provides versatility. **See pages 72-79**

For more information: Tool Selector; gedore-torque.com/tool-selector Telephone; +44 (0) 1483 894 476
Videos; www.youtube.com/gedore-torque Email; salesandrepairs@gedore-torque.com

Want to know how to use this tool?
YouTube
Watch our video

Order Code	Model	Calibrated Range				Drive	k	mm	g	Accuracy	ISO 6789 Class	
		ISO	Imperial	Imperial	Imperial							
017400	TT 50 FH	10-50 cN.m	2 cN.m	14-70 ozf-in	2 ozf-in		178	190	+/- 6%	1D	✓	
017500	TT 100 FH	20-100 cN.m	4 cN.m	28-140 ozf-in	4 ozf-in		178	190	+/- 6%	1D	✓	
017600	TT 250 FH	50-250 cN.m	10 cN.m	4-20 lbf-in	0.5 lbf-in		250	465	+/- 6%	1D	✓	
017700	TT 500 FH	100-500 cN.m	20 cN.m	8-40 lbf-in	1 lbf-in		250	465	+/- 6%	1D	✓	