


KEMET Part Number: C1210X393KFRAC7800
(C1210X393KFRAC7800)

Ceramic, FlexTerm-(CxxxxX), 0.039 uF, 10%, 1,500 V, 1210, X7R, SMD, MLCC, FT-CAP, Temperature Stable



CeramicChipSMDNoS
© 2011 Kemet Electronics Inc.
All rights reserved

Dimensions

L	3.3mm +/-0.4mm
W	2.6mm +/-0.3mm
T	2.5mm +/-0.30mm
B	0.6mm +/-0.25mm

Packaging Specifications

Packaging:	T&R, 180mm, Plastic Tape
Packaging Quantity:	1000

General Information

Style:	SMD Chip
Series:	FlexTerm-(CxxxxX)
Chip Size:	1210
Description:	SMD, MLCC, FT-CAP, Temperature Stable
Features:	FT-CAP, Temperature Stable
RoHS:	Yes
Termination:	Flexible Termination
Marking:	No
Failure Rate:	N/A
Miscellaneous:	Note: Referee time for X7R dielectric for this part number is 1000 hours

Specifications

Capacitance:	0.039 uF
Capacitance Tolerance:	10%
Voltage DC:	1500 VDC
Dielectric Withstanding Voltage:	1,800 V
Temperature Range:	-55/+125C
Temperature Coefficient:	X7R
Dissipation Factor:	2.5%
Aging Rate:	3% Loss/Decade Hour
Insulation Resistance:	2.564 GOhms