

PRODUCT DATASHEET

P PAR 30 77 30° 8 W/827 E27

PARATHOM PAR30 ADVANCED | Dimmable LED reflector lamps PAR30 with retrofit pin base



AREAS OF APPLICATION

- Display cabinets and shop windows
- Museums, art galleries
- Exhibition rooms
- Hospitality
- Residential interiors
- As a downlight for marking walkways, doors, stairs, etc.
- Outdoor applications only in suitable luminaires

PRODUCT BENEFITS

- Low energy consumption
- Easy replacement of halogen lamps thanks to compact design
- Instant 100 % light, no warm-up time

PRODUCT FEATURES

- Professional LED alternative to PAR30 lamps
- Good color rendering index $R_a: \geq 80$
- Dimmable (with many common dimmers, see also www.ledvance.com/dim)
- Mercury-free lamps



TECHNICAL DATA
Electrical data

Rated wattage	8.00 W
Nominal wattage	8.00 W
Nominal voltage	220...240 V
Claimed equiv. conventional lamp power	77 W
Operating frequency	50...60 Hz
Power factor λ	> 0.90


Photometrical data

Luminous intensity	2000 cd
Nominal luminous flux	650 lm
Rated luminous flux	650 lm
Color temperature	2700 K
Color rendering index Ra	≥ 80
Lumen main.fact.at end of nom.life time	0.70
Light color (designation)	Warm White
Standard deviation of color matching	≤ 6 sdcn
Nominal useful luminous flux 90°	650 lm
Rated useful luminous flux 90°	650 lm
Rated peak intensity	2000 cd
Nom. useful luminous flux 120°	680 lm
Rated useful luminous flux 120°	680 lm

Light technical data

Beam angle	30 °
Warm-up time (60 %)	< 0.50 s
Starting time	< 0.5 s
Nominal beam angle	30 °
Rated beam angle (half peak value)	30.00 °

Dimensions & weight



Overall length	115.0 mm
Diameter	95.0 mm
Outer bulb	PAR95
Length	115.0 mm
Maximum diameter	95.0 mm

Lifespan

Nominal lamp life time	25000 h
Rated lamp life time	25000 h
Number of switching cycles	100000

— Additional product data

Base (standard designation)	E27
Mercury content	0.0 mg
Mercury-free	Yes
Show WEEE picto	Yes
Product remark	All technical parameters apply to the entire lamp/Due to the complex production process for light-emitting diodes, the typical values shown for the technical LED parameters are purely statistical values that do not necessarily match the actual technical parameters of each individual product, which can vary from the typical value

Capabilities

Dimmable	Yes
-----------------	-----

Certificates & standards

Energy efficiency class	A+
Energy consumption	8 kWh/1000h

Country specific categorizations

ILCOS	DRPAR-10/827-220-240-E27-96/36
Order reference	PPAR30D7730 8W/

LOGISTICAL DATA

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4052899954892	P PAR 30 77 30° 8 W/827 E27	Shipping carton box 15	512 mm x 311 mm x 162 mm	25.80 dm ³	5497.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

REFERENCES / LINKS

For dimming conformity see

▶ www.ledvance.com/dim

For further products and actual information concerning LED lamps see

▶ www.ledvance.com/ledlamps

For Guarantee see

▶ www.ledvance.com/guarantee

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.