XLR MIC Connector

pro-**signal**





Electrical Specifications


Contact Resistance
Insulator Resistance
Current Rating
Voltage Proof

: 5mΩ max.
: 5,000MΩ min.
: 4P/10A
: 125V AC

Diagram








26.5 Chart one

Dimensions : Millimetres



No.	Description	Material	Finish	Qty.
1	Die-Cast Shell	ZZnAL4-0	Nickel	1
2	Insulator	PA	Black	1
3	Seal	Rubber	Black	1
4	Latch	Stainless Steel	Tin	1
5	Push Button	ZZnAL4-0	Nickel	1
6	Chuck	POM	White	1
7	Сар	PA	Black	1
8	T-Ring	POM	White	1
9	Boot	PVC	Black	1
10	Female Pin	Phosphor Bronze	Silver	4
11	Pin	H59-1	Silver	4

Part Number Table

Description	Part Number	
Connectors, 4P XLR Female MIC Connector	PS000019	

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage raising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-SIGNAL is the registered trademark of the Group. © Premier Farnell Limited 2016.

www.element14.com www.farnell.com www.newark.com www.cpc.co.uk

