

## 1. Identification of the substance/preparation and company

### Product name

Alkaline batteries non-rechargeable

### Details of the supplier of the safety data sheet

Premier Farnell  
150 Armley Road  
Leeds LS12 2QQ  
Tel. : +44 (0) 870 129 8608

### Emergency telephone number

+44 (0) 870 202530

## 2. Composition /Information on Ingredients

Chemical Nature : Mixture  
CAS-No/EINECS NO.: Not applicable : Dangerous ingredients which have to be mentioned acc. To 99/45/EEC and it adaptations

Chemical Name	Hazardous%	CAS No.	TLV (UNITS)
Manganese Dioxide	36-43	1313-13-9	5 mg/m <sup>3</sup>
Zinc	13-18	7440-66-6	10 mg ZnO/m <sup>3</sup>
Potassium Hydroxide (40%)	4-9	1310-58-3	2 mg/m <sup>3</sup>
Graphite, natural	1-4	7782-42-5	2 mg/m <sup>3</sup>
Zinc Oxide	<1	1314-13-2	10 mg/m <sup>3</sup>

## 3. Hazards identifications

General : The Common known rules for handing of chemicals should be obeyed.  
Do not eat drink the product.

Physical-Chemical Hazards : This preparation is not classified as dangerous according to the criteria of directive 99/45/EEC

Hazards to man : LD50-LC50 Mixture: LD 50 oral rat is unknown  
Route of entry - Inhalation: NO  
Route of entry - Skin: YES  
Route of entry - Ingestion: NO  
No health hazard unless battery ruptures. In that event, it may cause burns and irritation.

Hazards to environment : Not applicable.

## 4. First-aid measures

Inhalation : Not anticipated. If battery is leaking, contents may be irritating to respiratory passages. Remove to fresh air. Contact physician if irritation persists.

Skin Contact : Not anticipated. If battery is leaking, irrigate exposed skin with copious amounts of clear, tepid water for at least 15 minutes. If irritation, injury or pain persists, consult a physician.

Eye contact : Not anticipated. If battery is leaking and material contacts eyes, flush with copious amounts of clear, tepid water for 30 minutes. Contact physician at once.

Ingestion : Not anticipated. Rinse the mouth and surrounding area with clear, tepid water for at least 15 minutes. Consult a physician immediately for treatment and to rule out involvement of the esophagus and other tissues.

**Notes to Physician:**

- 1) The primary acutely toxic ingredient is concentrated (40%) potassium hydroxide.
- 2) Anticipated potential leakage of potassium hydroxide is 1-3 ml, depending on battery size.
- 3) This SDS does not include or address the small button cell batteries, which can be ingested.

## 5. Fire-fighting measures

Suitable extinguishing media : As appropriate for surrounding area.  
Exposure hazards from combustion products : In case of fire, thermal degradation may produce hazardous fumes of zinc and manganese; hydrogen gas; caustic vapors of potassium hydroxide and other toxic by-products.  
Personal protective equipment : Wear full protective clothing. Use self contained breathing apparatus.

## 6. Accidental release measures

Personal precautions : Notify safety personnel of large spills. Caustic potassium hydroxide may be released from leaking or ruptured batteries. Avoid eye or skin contact and inhalation of vapors. Increase ventilation. Clean-up personnel should wear appropriate protective wear.  
Environmental precautions : In the event of battery rupture, prevent released material from entering drains.  
Methods for cleaning up : In the event of battery rupture, collect all released material in plastic bag for waste disposal. Flush residue with Plenty of water. Care for well-Ventilated conditions. Recycle or dispose of the materials in an appropriate way.

## 7. Handling and storage

Store at room temperature. Avoid mechanical or electrical abuse. Do not short or install incorrectly. Batteries may explode, pyrolyze or vent if disassembled, crushed, recharged or exposed to high temperatures. Install batteries in accordance with equipment instructions. Do not mix battery systems, such as alkaline and zinc carbon, in the same equipment. Replace all batteries in equipment at the same time. Do not carry batteries loose in pocket or bag. Do not remove battery label.

## 8. Exposure controls/Personal protection

Exposition/ Technical measures : General ventilation under normal use conditions.  
Eye Protection : None under normal use conditions. Wear safety glasses when handling leaking batteries.  
Skin Protection : None under normal use conditions. Use neoprene, rubber or latex gloves when handling leaking batteries.  
Respiratory Protection : None under normal use conditions.  
Other : Keep batteries away from small children.

## 9. Physical and chemical properties

Appearance And Odor: N/R	Boiling Point: N/R	Melting Point: N/R
Vapor Pressure (MM Hg/70 F): N/R	Vapor Density (Air=1): N/R	Specific Gravity: N/R
Decomposition Temperature: UNKNOWN	Evaporation Rate And Ref: N/R	Solubility In Water: N/R

Percent Volatile By Volume: N/R  
Corrosion Rate (IPY): UNKNOWN

Viscosity: N/R  
Autoignition Temperature: N/R

pH: N/R

## 10. Stability and Reactivity

Stability : YES  
Condition to avoid (Stability) : Avoid electrical shorting.  
Materials to avoid : NOT APPLICABLE  
Hazardous decomposition products : Oxides or fumes of manganese, zinc, potassium hydroxide.  
Hazardous Poly Occur : NO  
Conditions To Avoid (Poly) : NOT APPLICABLE

## 11. Toxicological information

The product is multi component mixture for which no toxicological data exists.

## 12. Ecological information

In general, no ecological data is available for preparations.

## 13. Disposal considerations

Waste disposal method : Individual consumers may dispose of spent (used) batteries with household trash. It does not recommend that spent batteries be accumulated (quantities of five gallons or more should be disposed of in a secure landfill), if recycling is not possible, the product have to be disposed of in accordance with your local legislation and regulations. Do not incinerate, since batteries may explode at excessive temperatures.

## 14. Transport Information

Road (ADR/RID) : not regulated  
Air (ICAO/IATA) : not regulated  
Sea (IMDG) : not regulated

## 15. Regulatory Information

None

## 16. Other information

The information on this Safety Date Sheet (SDS) was obtained form current and reputable sources. However, the data is provided without any warranty; expressed or implied, regarding its correctness or accuracy. It is the user's responsibility to assume liability on loss, injury, damage, or expense resulting from improper use of this product.

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of the Group. © Premier Farnell Limited 2016.