



Material Safety Data Sheet

Revision Date October 9, 2012	Prepared by Howard Clark	Technical Information 1-800-201-8822 or support@mgchemicals.com
Head Office 9347 - 193 Street, Surrey, B.C., V4N 4E7		Emergency Phone Canutech (613) 996-6666 Collect 24 hrs

For updates please download from www.mgchemicals.com or fax requests to 1-800-708-9888

Section 1: Product Identification

MSDS Code: NLAL TUSP

Name: Touch up spray paint

Use: For painting

Related to stock codes: All MG stock codes beginning with X or XS

Section 2: Hazardous Ingredients:

CAS#	Chemical Name	Percentage by weight	ACGIH TWA	Osha Pel	Osha Stel
811-97-2	1,1,1,2 - tetrafluoroethane	45	1000ppm	n/e	n/e
67-64-1	2-propanone	28 - 29	750ppm	1000ppm	1000ppm
108-65-6	1-methoxy-2-propanol acetate	2 - 3	n/e	n/e	n/e
141-78-6	ethyl acetate	1 - 2	400ppm	400ppm	n/e
110-43-0	2-heptanone	2 - 3	50ppm	100ppm	n/e
110-19-0	isobutyl acetate	2 - 3	150ppm	150ppm	n/e
108-88-3	toluene	6 - 8	50ppm	100ppm	150ppm
13463-67-7	titanium dioxide	0 - 4	5mg/m ³	5mg/m ³	n/e
64-17-5	ethyl alcohol	2 - 3	1000ppm	1000ppm	1000ppm
1330-20-7	xylene	1 - 3	100ppm	100ppm	150ppm
67-63-0	2-propanol	0 - 1	400ppm	400ppm	500ppm

Section 3: Hazards Identification

WHMIS Codes A, B5, D2A

NFPA Ratings: Health 1 Flammability 4 Reactivity 0

HMIS Rating: Health 1 Flammability 4 Reactivity 0

Eyes: Causes severe eye irritation, tearing, redness, and blurred vision. Vapors from this product are irritating to the eye.

Skin: May cause skin irritation. May cause defatting of skin.

Inhalation: Product is irritating to the nose, throat, and respiratory tract. May cause liver and kidney damage, and central nervous system depression.

Ingestion: Harmful if swallowed. Ingestion of large amounts may cause nausea, gastrointestinal upset, and pain. May cause liver and kidney damage, and central nervous system depression.

Chronic: May cause liver and kidney damage.

Section 4: First Aid Measures

Eyes: Remove contact lenses. Flush with water or saline for 15 minutes. Get medical aid.

Skin: Wash skin with large quantities of soap and water. Get medical aid if symptoms persist.

Inhalation: Immediately remove from exposure to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get medical aid.



Ingestion: Do not induce vomiting. If conscious, give 1-2 glasses of water. Get medical aid.

Section 5: Fire Fighting Measures

Autoignition Temperature:	n/e	Flash Point: -18°C	LEL / UEL: 1 / 15
Extinguishing Media:	Use water spray, dry chemical, carbon dioxide, or chemical foam.		
General Information:	Will burn if involved in a fire. Containers may explode in the heat of a fire. Flash back along vapor trail is possible.		

Section 6: Accidental Release Measures

Spill Procedure: Remove all sources of ignition. Provide adequate ventilation. Wear appropriate personal protection. Sprinkle absorbent compound onto spill, then sweep into a plastic or metal container. Wipe up further residue with paper towel and place in container. Wash spill area with soap and water.

Section 7: Handling and Storage

Handling: Wash thoroughly after handling. Avoid contact with eyes, skin, and clothing. Do not ingest or inhale. Do not expose container to heat or flame.

Storage: Keep away from sources of ignition. Store in a cool, dry, well ventilated area, away from incompatible substances. Keep from freezing.

Section 8: Exposure Controls

Routes of entry: Eyes, ingestion, inhalation, and skin.

Ventilation: Use adequate general or local exhaust ventilation to keep airborne concentrations below exposure limits.

Personal Protection: Wear appropriate protective eyeglasses or chemical safety goggles. Wear appropriate protective clothing to prevent skin contact. Use a NIOSH approved respirator when necessary.

Section 9: Physical and Chemical Properties

Physical State:	Aerosol	Odor: ethereal	Solubility: partial	Evaporation Rate: fast
Boiling Point:	n/a	Specific Gravity: 0.85	Vapor Pressure: 48 PSI @21°C	Vapor Density: 4.1 (Air=1) pH: 7

Section 10: Stability and Reactivity

Stability: Stable at normal temperatures and pressures.

Conditions to avoid: Temperatures over 40°C, ignition sources, and incompatible substances.

Incompatibilities: Alkali and alkaline earth metals, powdered aluminum, zinc, magnesium, and beryllium, strong oxidizers, and strong acids

Polymerization: Will not occur.

Decomposition: Halogens, halogen acids, possibly carbonyl halides, carbon dioxide, and carbon monoxide, nitrogen oxides

Section 11: Toxicological Information

Sensitization: (effects of repeated exposure)	Prolonged or repeated skin contact may cause dermatitis.
Carcinogenicity: (risk of cancer)	No
Teratogenicity: (risk of malformation in an unborn fetus)	This product contains xylene, a known embryotoxin. Pregnant women must avoid all contact with this product.
Reproductive Toxicity: (risk of sterility)	Toluene is listed under California Proposition 65 under chemicals



known to cause reproductive toxicity.

Mutagenicity: (risk of heritable genetic effects)

No

Lethal Exposure Concentrations:

Ingestion(LD50): 7400 mg/kg (rat)

Inhalation (LC50): 1600 ppm/4h (rat)

Skin (LD50): n/e

Section 12: Ecological Information

General Information: Avoid runoff into storms and sewers which lead into waterways. Water runoff can cause environmental damage.

Environmental Impact Data:

CFC: 0 **HFC:** 45% **Cl.Solv.:** 0 **HCFC:** 0 **ODP:** 0

Volatile Organic Compounds, % by weight: 18.0%

Volatile Organic Compounds, grams per liter: 153 g/L

Section 13: Disposal Information

General Information: Dispose of in accordance with all local, provincial, state, and federal regulations. Water runoff can cause environmental damage.

Section 14: Transportation Information

Ground:

Consumer Commodity, ORM-D.

Air:

Shipper must be trained and certified. Refer to IATA regulations.

Sea:

Un# 1950. Class 2.1. Shipper must be trained and certified. Refer to IMDG regulations.

Section 15: Regulatory Information

This product has been classified in accordance with the hazard criteria of the Controlled Products Regulations and the MSDS contains all of the information required by the Controlled Products Regulations.

SARA (Superfund Amendments and Reauthorization Act of 1986, USA, 40 CFR 372.4)

None of the chemicals in this product have a reportable quantity.

EPCRA (Emergency Planning and Right to Know Act, USA, 40 CFR 372.45)

This product contains the following chemicals subject to the reporting requirements of section 313 Title III of the SARA of 1986 and 40 CFR part 372: Methanol (CAS #67-56-1, 1% by weight)

TSCA (Toxic Substances Control Act of 1976, USA)

All substances are TSCA listed.

CAA (Clean Air Act, USA)

This product does not contain any class 1 ozone depletors.

This product does not contain any class 2 ozone depletors.

This product contains methanol (CAS #67-56-1, 1% by weight), listed as a hazardous air pollutant.

California Proposition 65 (Chemicals know to cause cancer or reproductive toxicity, May 1, 1997 revision, USA)

This product contains toluene, listed under chemicals know to the state to cause reproductive toxicity.

Health Canada

Labeling and containers used in this product are listed in compliance with Consumer Chemicals and Container regulations.

Environment Canada



Chemicals in this product are listed on the Domestic Substances List in the Canadian Environmental Protection Act

This product does not contain any ozone depleting substances.

Industry and Science Canada

Labeling, product identity, net quantity declaration, minimum printing type size heights, and packaging of this product is in compliance with the Consumer Packaging and Labeling Act and Regulations. This product is not slack filled in accordance to chapter 4 prohibitions.

RoHS (The restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2004).

This product is RoHS compliant.

Section 16: Other Information

Definitions: n/a = not applicable, n/e = not established

Disclaimer: This material safety data sheet is provided as an information resource only. M.G. Chemicals believes the information contained herein is accurate and compiled from reliable sources. It is the responsibility of the user to verify its validity. The buyer assumes all responsibility of using and handling the product in accordance with federal, state, and local regulations.