# Product data sheet Characteristics

## RL10013

#### REACTOR DRIVE LINE 3PH 75HP 5% 460V T-1



#### Complementary

[In] rated current 100 A

AWG gauge AWG 6...AWG 1/0

Depth 13.09 in

Electrical connection Screw clamp terminal

Height 13 in

Permissible voltage <= 600 V AC
Product weight 92 lb(US)

Protection type Harmonic distortion

Current protection
Overvoltage protection

Width 13.22 in

#### **Environment**

Product certifications CE

CSA LR29753

UL listed file E180243

#### Ordering and shipping details

Category 22062 - LINE REACTORS/FILTERS (RL,KLC)

GTIN 00785901142775

Nbr. of units in pkg.1Package weight(Lbs)92ReturnabilityNCountry of originUS

### Contractual warranty

Warranty period

18 months