



## Main

Range of product	Preventa Safety detection
Product or component type	Safety switch
Component name	XCSL
Head type	Key operated turret head

## Complementary

Positive opening	With NC contact
Supply voltage type	AC/DC
Supply frequency	50/60 Hz
Load factor	1
Power consumption in VA	10 VA (inrush) 10 VA (sealed)
Signalling circuit consumption	7 mA
Mechanical durability	>= 1000000 cycles
Maximum load current	<= 15 A
[Uimp] rated impulse withstand voltage	6 kV conforming to EN/IEC 60947-5-1
Protection type	Overvoltage protection signalling circuit
Operating rate	10 cyc/mn for maximum durability
Safety level	Can reach category 4 with the appropriate monitoring system and correctly wired conforming to EN/ISO 13849-1 Can reach PL = e with the appropriate monitoring system and correctly wired conforming to EN/ISO 13849-1 Can reach SIL 3 with the appropriate monitoring system and correctly wired conforming to EN/IEC 61508

## Environment

Protective treatment	TC
----------------------	----

Class of protection against electric shock	Class I conforming to EN/IEC 60536
--	------------------------------------

**Ordering and shipping details**

Category	22411 - LIMIT SWITCHES,IEC,XCKJ
GTIN	00785901390725
Nbr. of units in pkg.	1
Package weight(Lbs)	2.1200000000000001
Returnability	Y
Country of origin	FR

**Offer Sustainability**

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1136 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product end of life instructions	Need no specific recycling operations

**Contractual warranty**

Warranty period	18 months
-----------------	-----------