

Aluminum Electrolytic, 85C, ALS71, 2400 uF, 20%, 350 V, -40/+85C



Dimensions	
D	51mm +/-1mm
L	82mm +/-2mm
T	5.5mm +/-0.5mm
S	22.2mm +/-0.5mm
DT	13mm +/-0.5mm
LT	86.5mm +/-1mm
TD	10mm MIN
V	13.7mm NOM
Z	10mm NOM

Packaging Specifications	
Weight:	220 g
Sleaving:	Yes
Packaging:	T&R

General Information	
Dielectric:	Aluminum Electrolytic
Series:	ALS71
Description:	Screw Terminal, Aluminum Electrolytic
RoHS:	Yes
Notes:	Dimensions D And L Include Sleaving. MS (MxH) = M12x 16

Specifications	
Capacitance:	2400 uF
Capacitance Tolerance:	20%
Voltage DC:	350 VDC, 385 VDC (Surge), 500 VDC (Surge)
Temperature Range:	-40/+85C
Rated Temperature:	85C
Life:	2000 Hrs
Resistance:	80 mOhms (100Hz 20C), 49 mOhms (10kHz 20C)
Current:	8.1 Amps (100Hz 85C), 13.6 Amps (10 kHz 85C)
Leakage:	5040 uAmps (5min 20C)