



### Main

Device short name	OF SD
Product or component type	Auxiliary contact
Range compatibility	PowerPact PowerPact B Compact Compact NSXm
Signal contacts composition	1 NO/NC

### Complementary

Auxiliary contacts type	Standard
Mounting mode	Clip-on
[I <sub>th</sub> ] conventional free air thermal current	5 A

[I <sub>e</sub> ] rated operational current	<p>Utilisation category DC-12 : 0.3 A network: DC at 250 V</p> <p>Utilisation category DC-14 : 0.03 A network: DC at 250 V</p> <p>Utilisation category AC-12 : 5 A network: AC/DC 50/60 Hz at 24 V</p> <p>Utilisation category AC-12 : 5 A network: AC/DC 50/60 Hz at 48 V</p> <p>Utilisation category AC-12 : 5 A network: AC/DC 50/60 Hz at 110 V</p> <p>Utilisation category AC-12 : 5 A network: AC 50/60 Hz at 220...240 V</p> <p>Utilisation category AC-12 : 5 A network: AC 50/60 Hz at 380...440 V</p> <p>Utilisation category AC-12 : 5 A network: AC 50/60 Hz at 660...690 V</p> <p>Utilisation category AC-15 : 5 A network: AC/DC 50/60 Hz at 24 V</p> <p>Utilisation category AC-15 : 5 A network: AC/DC 50/60 Hz at 48 V</p> <p>Utilisation category AC-15 : 4 A network: AC/DC 50/60 Hz at 110 V</p> <p>Utilisation category AC-15 : 3 A network: AC 50/60 Hz at 220...240 V</p> <p>Utilisation category AC-15 : 2.5 A network: AC 50/60 Hz at 380...440 V</p> <p>Utilisation category AC-15 : 0.1 A network: AC 50/60 Hz at 660...690 V</p> <p>Utilisation category DC-12 : 5 A network: AC/DC 50/60 Hz at 24 V</p> <p>Utilisation category DC-12 : 2.5 A network: AC/DC 50/60 Hz at 48 V</p> <p>Utilisation category DC-12 : 0.6 A network: AC/DC 50/60 Hz at 110 V</p> <p>Utilisation category DC-14 : 2.5 A network: AC/DC 50/60 Hz at 24 V</p> <p>Utilisation category DC-14 : 1.2 A network: AC/DC 50/60 Hz at 48 V</p> <p>Utilisation category DC-14 : 0.35 A network: AC/DC 50/60 Hz at 110 V</p> <p>Utilisation category DC-14 : 0.05 A network: DC at 250 V</p> <p>Utilisation category DC-14 : 1 A network: AC/DC 50/60 Hz at 24 V</p> <p>Utilisation category DC-14 : 0.2 A network: AC/DC 50/60 Hz at 48 V</p> <p>Utilisation category DC-14 : 0.05 A network: AC/DC 50/60 Hz at 110 V</p>
---	---

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Minimum load	5 mA at 17 V DC
Auxiliary connection terminal	Spring
Wire stripping length	8 mm front
Length	1 mm

### Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 1649 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>