

The SW60P is a miniature series single pole, free standing, compact contactor which is sealed to IP66. The SW60P designed to fill the gap between 30 ampere relays and 100 ampere contactors. Devised for both interrupted and uninterrupted loads, the SW60P is suitable for switching Resistive, Capacitive and Inductive loads. Typical applications power packs and small electric winch motors.


uninterrupted loads, the Sinclude switching small tr						
Application	Interru		Uninterrupt		Ė	
Thermal Current Rating ( <sup>1</sup> th)		80	)A		•	
Intermittent Current Rating:						
30% Duty		14	5A		•	
40% Duty		12:	5A			
50% Duty		11	5A		I	
60% Duty		10:			S	
70% Duty		95			a	
Rated Fault Current Breaking Capac (in accordance with UL583*)	city ( <sup>/</sup> cn) s				n	
SW60P	400A at 48V D.C.				C	
SW60BP	400A at 96V D.C.				_	
Rated Fault Current Breaking Capac (in accordance with UL508*)	city ( <sup>/</sup> cn) f	ity ( <sup>/</sup> cn) Resistive Load:				
SW60P	1	120A at 60V D.C.				
SW60BP	1	120A at 96V D.C.				
Maximum Recommended Contact V	oltages (	U <sub>e</sub> ):			1	
SW60P	48V [	D.C.	60V D.C.			
SW60BP		96V	D.C.			
Typical Voltage Drop per pole across New Contacts at 80A		<40mV				
Mechanical M.T.B.F		>3 x 10 <sup>6</sup>				
Coil Voltage Available (U <sub>S</sub> ) (Rectifier board required for A.C.)	Fro	om 6 to	130V D.C.			
Coil Power Dissipation:						
Highly Intermittent Rated Types		14 - 21	Watts		1	
Intermittently Rated types		10 - 14	Watts			
Prolonged Rated Types		7 - 10	Watts			
Continuously Rated Types		5 - 7 Watts				
Maximum Pull-In Voltage (Coil at 20	°C) Guid	eline:				
Highly Intermittent Rated types (Max 25% Duty Cycle)	60% U <sub>S</sub>			1		
Intermittently Rated types (Max 70% Duty Cycle)		60% U <sub>S</sub>				
Prolonged Operation (Max 90% Duty Cycle)	60% U <sub>s</sub>			1		
Continuously Rated Types (100% Duty Cycle)		66% U <sub>S</sub>				
Drop-Out Voltage Range		10 - 25% U <sub>S</sub>		1	E	
Typical Pull-In Time	15ms			1	E	
Typical Drop-Out Time (N/O Contact	ts to Ope	n):			Ė	
Without Suppression	6ms				Ė	
With Diode Suppression		35ms		4		
With Diode and Resistor (Subject to resistance value)		8 - 20ms		4		
Typical Contact Bounce Period		3n	าร	1		
Operating Ambient Temperature		- 40°C to	o + 60°C			
Guideline Contactor Weight:						
SW60P		210	gms			
With Blowouts		+ 8 (	gms			
Advised Connection Sizes for Ma	ximum C	ontinuc	us Current			
Copper busbar	5	2mm² [0	.08inch <sup>2</sup> ]			
Cable	Rated	suitable	for Application	n 🗸		


- Interrupted current opening and closing on load with frequent switching (results in increased contact resistance).
- Uninterrupted current no or infrequent load switching requirements (maintains a lower contact resistance).


The SW60P features single pole double breaking main contacts with silver alloy tips, which are weld resistant, hard wearing and have excellent conductivity. The SW60P incorporates an enclosed top cover and offers environmental protection to IP66. The SW60P has M6 stud main terminals and 6.3mm spade coil connections. It can be mounted via mounting brackets (supplied fitted). Mounting can be on the side or base of the contactor.











Auxiliary Contacts - V4	X					
Magnetic Blowouts†	0	В				
Magnetic Blowouts - High Powered <sup>†</sup>	X					
Armature Cap	X					
Mounting Brackets (See Stud Series Catalogue)	•					
Magnetic Latching† (Not fail safe)	0	М				
Closed Contact Housing	•					
Environmentally Protected IP66	•	Р				
EE Type (Steel Shroud)	X					
Contacts						
Large Tips	X					
Textured Tips	X					
Silver Plating	X					
Coil						
AC Rectifier Board (Fitted)	X					
Coil Suppression <sup>†</sup>	0					
Flying Leads	X					
Manual Override Operation	X					
M4 Stud Terminals	0					
M5 Terminal Board X						
Vacuum Impregnation X						
<b>Key:</b> Optional ○ Standard • Not Available X						
† Connections become polarity sensitive						

SW60P Available Options

**Auxiliary Contacts** 

- Performance data provided should be used as a guide only. Some de-rating or variation from figures may be necessary according to application.
- Thermal current ratings stated are dependant upon the size of conductor being used
- For further technical advice email: technical@albrightinternational.com
- Albright reserve the right to change data without prior notice

**Key: ▼** = Interrupted **△** = Uninterrupted Note: Where applicable values shown are at 20°C \* Please check our web site for product UL status

Interrupted and Uninterrupted Current Suffix

Х