


**KEMET Part Number: C0603Y223K5RACTU**  
(C0603Y223K5RAC7867)

Ceramic, Floating Electrode, FloatingFlexTerm-(CxxxxY), 0.022 uF, 10%, 50 V, 0603, X7R, SMD, MLCC, FF-CAP, Floating Electrode



**Dimensions**

|          |                  |
|----------|------------------|
| <b>L</b> | 1.6mm +/-0.17mm  |
| <b>W</b> | 0.8mm +/-0.15mm  |
| <b>T</b> | 0.8mm +/-0.15mm  |
| <b>S</b> | 0.58mm MIN       |
| <b>B</b> | 0.45mm +/-0.15mm |

**Packaging Specifications**

|                            |                        |
|----------------------------|------------------------|
| <b>Packaging:</b>          | T&R, 180mm, Paper Tape |
| <b>Packaging Quantity:</b> | 4000                   |

**General Information**

|                       |                                                                          |
|-----------------------|--------------------------------------------------------------------------|
| <b>Style:</b>         | SMD Chip                                                                 |
| <b>Series:</b>        | FloatingFlexTerm-(CxxxxY)                                                |
| <b>Chip Size:</b>     | 0603                                                                     |
| <b>Description:</b>   | SMD, MLCC, FF-CAP, Floating Electrode                                    |
| <b>Features:</b>      | FF-CAP, Floating Electrode                                               |
| <b>RoHS:</b>          | Yes                                                                      |
| <b>Termination:</b>   | Flexible Termination                                                     |
| <b>Marking:</b>       | No                                                                       |
| <b>Failure Rate:</b>  | N/A                                                                      |
| <b>Miscellaneous:</b> | Note: Referee time for X7R dielectric for this part number is 1000 hours |

**Specifications**

|                                         |                     |
|-----------------------------------------|---------------------|
| <b>Capacitance:</b>                     | 0.022 uF            |
| <b>Capacitance Tolerance:</b>           | 10%                 |
| <b>Voltage DC:</b>                      | 50 VDC              |
| <b>Dielectric Withstanding Voltage:</b> | 125 V               |
| <b>Temperature Range:</b>               | -55/+125C           |
| <b>Temperature Coefficient:</b>         | X7R                 |
| <b>Dissipation Factor:</b>              | 2.5%                |
| <b>Aging Rate:</b>                      | 3% Loss/Decade Hour |
| <b>Insulation Resistance:</b>           | 4.545 GOhms         |