

Capacitor, Ceramic, SMD, MLCC, Ultra-Stable, Low Loss, Auto Grade, 100 pF, +/-5% Tol, 25 V, COG, 0402 (1005 metric)



| General Information | |
|--------------------------|---|
| Supplier: | KEMET |
| Application: | Automotive (AEC-Q200 Qualified) |
| Chip Size: | 0402 (1005 metric) |
| Temperature Coefficient: | COG |
| Part Type Description: | SMD, MLCC, Ultra-Stable, Low Loss, Auto Grade |
| Termination Type: | Tin (Sn) |
| Marked: | No |
| RoHS: | Yes |
| Approvals: | AEC-Q200 |

| Dimensions (mm) | | |
|-----------------|-----------|-----------|
| Symbol | Dimension | Tolerance |
| L | 1 | +/-0.05 |
| W | 0.5 | +/-0.05 |
| T | 0.5 | +/-0.05 |
| B | 0.3 | +/-0.1 |
| S | 0.3 | MIN |

| Specifications | |
|------------------------|---------------------|
| Capacitance: | 100 pF |
| Voltage: | 25 V |
| Tolerance: | +/-5% |
| Temperature Range: | -55/+125C |
| Dissipation Factor: | 0.1% |
| Failure Rate: | N/A |
| Aging Rate: | 0% loss/decade hour |
| Insulation Resistance: | 100 GOhm |
| Dielectric Strength: | 62.5 V |

| Packaging Specifications | |
|--------------------------|-------------|
| Package Kind: | T&R |
| Package Size: | 7 in/180 mm |
| Package Type: | Paper Tape |
| Package Quantity: | 10000 |