


Tantalum, Polymer Tantalum, Reduced Volume, T527, 100 uF, 20%, 6.3 V, 3216, SMD, Polymer, Molded, Face Down Terminals, 100 mOhms, Height Max = 1mm



TantChipBlackFD
 © 2013 Intellicore Inc. All rights reserved.

General Information

Dielectric:	Polymer Tantalum
Style:	SMD Chip
Series:	T527
Description:	SMD, Polymer, Molded, Face Down Terminals
Features:	Face Down, Low Profile, Low ESR
RoHS:	Yes
Termination:	Tin

Dimensions

Footprint	3216
L	3.2mm +/-0.2mm
W	1.6mm +/-0.2mm
H	0.9mm +/-0.1mm
S	0.8mm +/-0.2mm
F	1.2mm +/-0.1mm

Packaging Specifications

Weight:	70.12 mg
Packaging:	T&R, 178mm
Packaging Quantity:	3000

Specifications

Capacitance:	100 uF
Capacitance Tolerance:	20%
Voltage DC:	6.3 VDC (85C), 5.04 VDC (105C)
Temperature Range:	-55/+105C
Dissipation Factor:	8% 120Hz 25C
Failure Rate:	N/A
Resistance:	100 mOhms (100kHz 25C)
Current:	775 mAmps (100kHz 45C), 697.5 mAmps (85C), 310 mAmps (105C)
Leakage Current:	63 uA (5min 25C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.