

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION


Part Number: 0022035055
Status: Active
Overview: SPOX™ Wire-to-Board Connectors
Description: 2.50mm Pitch SPOX™ Wire-to-Board Header, Vertical, Shrouded, 5 Circuits, Tin (Sn) Plating

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-5264-001-001 \(PDF\)](#)
[Packaging Specification SPK-5267-001-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
CSA LR19980
UL E29179

General
Product Family PCB Headers
Series 5267
Application Signal, Wire-to-Board
MolexKits Yes
Overview SPOX™ Wire-to-Board Connectors
Product Name SPOX™
UPC 800753591516

Physical
Breakaway No
Circuits (Loaded) 5
Circuits (maximum) 5
Color - Resin Natural
Durability (mating cycles max) 30
First Mate / Last Break No
Flammability 94V-0
Glow-Wire Compliant No
Guide to Mating Part No
Keying to Mating Part None
Lock to Mating Part Yes
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin Nylon
Net Weight 452.800/mg
Number of Rows 1
Orientation Vertical
PC Tail Length 3.50mm
PCB Locator No
PCB Retention Yes
PCB Thickness - Recommended 1.60mm
Packaging Type Bag
Pitch - Mating Interface 2.50mm
Plating min - Mating 4.064µm
Plating min - Termination 4.064µm
Polarized to Mating Part Yes
Polarized to PCB No
Shrouded Fully
Stackable No
Surface Mount Compatible (SMC) No
Temperature Range - Operating -40°C to +105°C
Termination Interface: Style Through Hole



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per
-ED/01/2017 (12
January 2017)
Halogen-Free
Status
Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[5267 Series](#)

Mates With
[5264](#) SPOX™ Wire-to-Board Crimp Housing, [42219](#) SPOX™ IDT Receptacle Housing

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	250V

Material Info

Engineering Number	5267-05A
--------------------	----------

Reference - Drawing Numbers

Packaging Specification	SPK-5267-001-001
Product Specification	PS-5264-001-001
Sales Drawing	SD-5267-NA

This document was generated on 05/01/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION