



Description


Heat shrinkable tube (Normal wall) is a newly developed environment-friendly flame retardant heat-shrinkable tube, using modified polymers and cross-linked by electronic accelerator. It offers an economic and efficient solution for the insulation and protection of cable splices and terminals.

It is widely used in the fields of electricity, communication, automotive for connection insulation and rust-proof of metallic product.

Technical data

Material : Polyethylene
 Shrinking Ratio : 2:1
 Operating Range : -55°C- + 125°C
 Start Shrunk Temperature : Start at 70°C and complete shrink at 110°C
 Longitudinal Shrinkage : $\leq 8\%$
 Flammability : VW-1
 Cutting Tool : Heat gun, Oven
 Clear heat shrinkable tube operating temperature is 105°C

Dimensions



Part Number	As supplied		After recovered	
	I.D. (D)	Wall thickness (t)	Max. I.D. (l)	Wall thickness (T)
MC001704	26 ±0.7	0.5 ±0.1	≤12.5	0.9 ±0.15
MC001755	13.5 ±0.5	0.35 ±0.06	≤6.5	0.7 ±0.1
MC001741	6.5 ±0.4	0.28 ±0.04	≤3	0.55 ±0.1
MC001773	13.5 ±0.5	0.35 ±0.06	≤6.5	0.7 ±0.1
MC001736	3.5 ±0.4	0.2 ±0.04	≤1.5	0.4 ±0.1
MC001702	5.5 ±0.4	0.25 ±0.04	≤2.5	0.5 ±0.1
MC001757	13.5 ±0.5	0.35 ±0.06	≤6.5	0.7 ±0.1
MC001730	13.5 ±0.5	0.35 ±0.06	≤6.5	0.7 ±0.1
MC001708	21 ±0.7	0.4 ±0.08	≤10	0.75 ±0.1
MC001689	13.5 ±0.5	0.35 ±0.06	≤6.5	0.7 ±0.1
MC001728	10.5 ±0.5	0.3 ±0.05	≤5	0.6 ±0.1
MC001706	10.5 ±0.5	0.3 ±0.05	≤5	0.6 ±0.1

Heat Shrink Tubing



Part Number	As supplied		After recovered	
	I.D. (D)	Wall thickness (t)	Max. I.D. (I)	Wall thickness (T)
MC001719	13.5 ±0.5	0.35 ±0.06	≤6.5	0.7 ±0.1
MC001753	3.5 ±0.4	0.2 ±0.04	≤1.5	0.4 ±0.1
MC001763	2.5 ±0.3	0.2 ±0.05	≤1	0.4 ±0.1
MC001758	13.5 ±0.5	0.35 ±0.06	≤6.5	0.7 ±0.1
MC001724	21 ±0.7	0.4 ±0.08	≤10	0.75 ±0.1
MC001745	13.5 ±0.5	0.35 ±0.06	≤6.5	0.7 ±0.1
MC001737	3.5 ±0.4	0.2 ±0.04	≤1.5	0.4 ±0.1
MC001771	5.5 ±0.4	0.25 ±0.04	≤2.5	0.5 ±0.1
MC001770	10.5 ±0.5	0.3 ±0.05	≤5	0.6 ±0.1
MC001687	2.5 ±0.3	0.2 ±0.05	≤1	0.4 ±0.1
MC001709	10.5 ±0.5	0.3 ±0.05	≤5	0.6 ±0.1
MC001732	2.5 ±0.3	0.2 ±0.05	≤1	0.4 ±0.1
MC001749	3.5 ±0.4	0.2 ±0.04	≤1.5	0.4 ±0.1
MC001723	5.5 ±0.4	0.25 ±0.04	≤2.5	0.5 ±0.1
MC001762	3 ±0.3	0.2 ±0.04	≤1.25	0.4 ±0.1
MC001729	21 ±0.7	0.4 ±0.08	≤10	0.75 ±0.1
MC001740	2.5 ±0.3	0.2 ±0.05	≤1	0.4 ±0.1
MC001754	21 ±0.7	0.4 ±0.08	≤10	0.75 ±0.1
MC001731	3.5 ±0.4	0.2 ±0.04	≤1.5	0.4 ±0.1
MC001676	5.5 ±0.4	0.25 ±0.04	≤2.5	0.5 ±0.1
MC001742	3 ±0.3	0.2 ±0.04	≤1.25	0.4 ±0.1
MC001759	1.5 ±0.2	0.18 ±0.03	≤0.65	0.36 ±0.1
MC001722	2.5 ±0.3	0.2 ±0.05	≤1	0.4 ±0.1
MC001720	5.5 ±0.4	0.25 ±0.04	≤2.5	0.5 ±0.1
MC001769	1.5 ±0.2	0.18 ±0.03	≤0.65	0.36 ±0.1
MC001711	1.5 ±0.2	0.18 ±0.03	≤0.65	0.36 ±0.1
MC001752	5.5 ±0.4	0.25 ±0.04	≤2.5	0.5 ±0.1
MC001679	5.5 ±0.4	0.25 ±0.04	≤2.5	0.5 ±0.1
MC001703	21 ±0.7	0.4 ±0.08	≤10	0.75 ±0.1
MC001717	26 ±0.7	0.5 ±0.1	≤12.5	0.9 ±0.15
MC001690	3 ±0.3	0.2 ±0.04	≤1.25	0.4 ±0.1
MC001772	10.5 ±0.5	0.3 ±0.05	≤5	0.6 ±0.1
MC001746	5.5 ±0.4	0.25 ±0.04	≤2.5	0.5 ±0.1
MC001751	10.5 ±0.5	0.3 ±0.05	≤5	0.6 ±0.1
MC001701	26 ±0.7	0.5 ±0.1	≤12.5	0.9 ±0.15

Heat Shrink Tubing



Part Number Table

Description	Part Number
Heat Shrink Tubing, 25.4mm ID, PO, Black, 20FT, PK of 2	MC001704
Heat Shrink Tubing, 12.7mm ID, PO, Black, PK of 14	MC001755
Heat Shrink Tubing, 6.35mm ID, PO, Transparent, 4FT, PK of 25	MC001741
Heat Shrink Tubing, 12.7mm ID, PO, Black, PK of 5	MC001773
Heat Shrink Tubing, 3.175mm ID, PO, Black, PK of 28	MC001736
Heat Shrink Tubing, 4.75mm ID, PO, Black, 4FT, PK of 25	MC001702
Heat Shrink Tubing, 12.7mm ID, PO, Black, PK of 5	MC001757
Heat Shrink Tubing, 12.7mm ID, PO, Black, 20FT, PK of 5	MC001730
Heat Shrink Tubing, 19.1mm ID, PO, Black, 4FT, PK of 5	MC001708
Heat Shrink Tubing, 12.7mm ID, PO, Black, 4FT, PK of 5	MC001689
Heat Shrink Tubing, 9.525mm ID, PO, Black, 6 IN, PK of 16	MC001728
Heat Shrink Tubing, 9.525mm ID, PO, Black, 8FT, PK of 16	MC001706
Heat Shrink Tubing, 12.7mm ID, PO, Black, 7FT, PK of 14	MC001719
Heat Shrink Tubing, 3.175mm ID, PO, Black, 14FT, PK of 28	MC001753
Heat Shrink Tubing, 1.6mm ID, PO, Black, 18FT, PK of 36	MC001763
Heat Shrink Tubing, 12.7mm ID, PO, Transparent, 4FT, PK of 5	MC001758
Heat Shrink Tubing, 19.1mm ID, PO, Black, 6 IN, PK of 12	MC001724
Heat Shrink Tubing, 12.7mm ID, PO, Black, 6 IN, PK of 14	MC001745
Heat Shrink Tubing, 3.175mm ID, PO, Black, 100FT, PK of 25	MC001737
Heat Shrink Tubing, 4.75mm ID, PO, Black, PK of 24	MC001771
Heat Shrink Tubing, 9.525mm ID, PO, 6IN PIECES, PK of 16	MC001770
Heat Shrink Tubing, 1.6mm ID, PO, Black, 100FT,	MC001687
Heat Shrink Tubing, 9.525mm ID, PO, Black, 4FT, PK of 25	MC001709
Heat Shrink Tubing, 1.6mm ID, PO, Black, PK of 25	MC001732
Heat Shrink Tubing, 3.175mm ID, PO, Transparent, 6 IN, PK of 28	MC001749
Heat Shrink Tubing, 4.75mm ID, PO, Black, 6 IN, PK of 24	MC001723
Heat Shrink Tubing, 2.36mm ID, PO, Black, PK of 32	MC001762
Heat Shrink Tubing, 19.1mm ID, PO, Black, 6FT, PK of 12	MC001729
Heat Shrink Tubing, 1.6mm ID, PO, Black, 4FT, PK of 25	MC001740
Heat Shrink Tubing, 19.1mm ID, PO, Transparent, 4FT, PK of 5	MC001754
Heat Shrink Tubing, 3.175mm ID, PO, Black, PK of 25	MC001731
Heat Shrink Tubing, 4.75mm ID, PO, Black, 100FT, PK of 25	MC001676
Heat Shrink Tubing, 3.175mm ID, PO, Black, 7FT, PK of 14	MC001742
Heat Shrink Tubing, 1.169mm ID, PO, Black, PK of 25	MC001759
Heat Shrink Tubing, 1.6mm ID, PO, Black, 6 IN, PK of 36	MC001722
Heat Shrink Tubing, 4.75mm ID, PO, Black, 12FT, PK of 24	MC001720
Heat Shrink Tubing, 1.169mm ID, PO, Black, 100FT, PK of 25	MC001769

Heat Shrink Tubing



Description	Part Number
Heat Shrink Tubing, 1.169mm ID, PO, Black, 4FT, PK of 25	MC001711
Heat Shrink Tubing, 4.75mm ID, PO, Black, PK of 25	MC001752
Heat Shrink Tubing, 4.75mm ID, PO, Black, 100FT,	MC001679
Heat Shrink Tubing, 19.1mm ID, PO, Black, 20FT, PK of 5	MC001703
Heat Shrink Tubing, 25.4mm ID, PO, Black, 4FT, PK of 5	MC001717
Heat Shrink Tubing, 2.36mm ID, PO, Black, 100FT,	MC001690
Heat Shrink Tubing, 9.525mm ID, PO, Black, PK of 16	MC001772
Heat Shrink Tubing, 4.75mm ID, PO, Black, 12FT, PK of 24	MC001746
Heat Shrink Tubing, 9.525mm ID, PO, Black, PK of 25	MC001751
Heat Shrink Tubing, 25.4mm ID, PO, Black, 50FT	MC001701

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell Limited 2016.

www.element14.com
www.farnell.com
www.newark.com

