

Transient Voltage Suppressor



Features:

- Glass passivated junction
- Low incremental surge resistance, excellent clamping capability
- 1,500W peak pulse power capability with a 10/1,000 μ s waveform, repetition rate (duty cycle): 0.01%
- Very fast response time
- High temperature soldering guaranteed : 250°C/10 secs at terminals

Mechanical Data:

- Case : JEDEC DO-214AB moulded plastic over glass passivated junction
- Polarity : For uni-directional types the colour band denotes the cathode, which is positive with respect to the anode under normal TVS operation
- Weight : 0.007 ounces, 0.21 grams
- Flammability : epoxy is rated UL 94V-0

Maximum Ratings & Characteristics: Tamb = 25°C, unless otherwise specified.

Description	Symbol	Values	Unit
Peak power dissipation with a 10/1,000 μ s waveform (Note1 & 2,)	PPPM	1.500 (Min.)	W
Peak pulse current with a 10/1,000 μ s waveform (Note1)	IPPM	See table below	A
Peak forward surge current, 8.3ms single half sine-wave unidirectional only (Note 2)	IFSM	200	A
Typical thermal resistance, junction to ambient (Note 3)	R _{thJA}	100	°C/W
Typical thermal resistance, junction to lead	R _{thJL}	20	°C/W
Operational junction and storage temperature range	T _J , T _{STG}	-55 to +150	°C

Notes:

1. Non-repetitive current pulses, per fig.3 and derated above TA = 25°C per fig.2
2. Mounted on 0.2 × 0.2" (5.0 × 5.0mm) copper pads to each terminal
3. Mounted on minimum recommended pad layout

Bi-Directional 1,500 Watt Surface Mount TVS

Part Number	Marking	Stand-off Voltage V _{WM} (V)	Breakdown Voltage V _{BR} (V) Min. at IT	Breakdown Voltage V _{BR} (V) Max. at IT	Test Current I _{test} (mA)	Max. Clamping Voltage V _{clamp} (V)	Peak Pulse Current I _{PP} (A)
SMCJ6.0CA+	BDG	6	6.67	7.67	10	10.3	145.6
SMCJ9.0CA+	BDV	9	10	11.5	1	15.4	97.4

Ratings & Characteristic Curves

FIG.1 – PEAK PULSE POWER RATING CURVE




FIG.3 – PULSE WAVEFORM




FIG.5 – TYPICAL TRANSIENT THERMAL IMPEDANCE




FIG.2 – PULSE DERATING CURVE




FIG.4 – TYPICAL JUNCTION CAPACITANCE UNIDIRECTIONAL






FIG.6 – MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT



Transient Voltage Suppressor



DO-214AB(SMC)



Dimensions : Millimetres

Part Number Table

Description	Part Number
Transient Voltage Suppressor, Bi-Directional 1,500 Watt	SMCJ6.0CA+
	SMCJ9.0CA+

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell Limited 2016.

www.element14.com
www.farnell.com
www.newark.com

