


**KEMET Part Number: T491A225K025AT**  
(B45196H5225K109)

Tantalum, MnO<sub>2</sub> Tantalum, T491, 2.2 uF, 10%, 25 V, 3216, SMD, MnO<sub>2</sub>, Molded, 7 Ohms, Height Max = 1.8mm



Dimensions	
Footprint	3216
L	3.2mm +/-0.2mm
W	1.6mm +/-0.2mm
H	1.6mm +/-0.2mm
T	0.13mm REF
S	0.8mm +0.2/-0.3mm
F	1.2mm +/-0.1mm
A	1.2mm MIN
B	0.4mm +/-0.15mm
E	1.3mm REF
G	1.1mm REF
P	0.4mm REF
R	0.4mm REF
X	0.1mm +/-0.1mm

Packaging Specifications	
Weight:	58.6 mg
Packaging:	T&R, 178mm
Packaging Quantity:	2000

General Information	
Dielectric:	MnO <sub>2</sub> Tantalum
Style:	SMD Chip
Series:	T491
Description:	SMD, MnO <sub>2</sub> , Molded
RoHS:	Yes
Termination:	Tin

Specifications	
Capacitance:	2.2 uF
Capacitance Tolerance:	10%
Voltage DC:	25 VDC (85C), 16.75 VDC (125C)
Temperature Range:	-55/+125C
Dissipation Factor:	6% 120Hz 20C
Failure Rate:	N/A
Resistance:	7 Ohms (100kHz)
Current:	104 mAmps (100kHz 25C), 93.6 mAmps (85C), 41.6 mAmps (125C)
Leakage Current:	0.6 uAmps (5min 20C)