


Ceramic, Commercial Grade, GoldMax, 0.1 uF, 20%, 50 V, X7R, Lead Spacing = 5.08mm



#### Dimensions

L	5.08mm MAX
H	7.62mm MAX
T	3.18mm MAX
S	5.08mm NOM
LL	7mm MIN
F	0.51mm NOM

#### Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	500

#### General Information

Style:	Radial
Series:	GoldMax
Description:	GoldMax, Commercial Standard
RoHS:	Yes
Termination:	Tin
Failure Rate:	N/A

#### Specifications

Capacitance:	0.1 uF
Capacitance Tolerance:	20%
Voltage DC:	50 VDC
Temperature Range:	-55/+125C
Temperature Coefficient:	X7R
Dissipation Factor:	2.5%
Aging Rate:	3% Loss/Decade Hour
Insulation Resistance:	10 GOhms
Dielectric Strength:	125 V