

Polymer Aluminum, 105C LowZ, A750, 560 uF, 20%, 10 V, -55/+105C, Lead Spacing = 3.5mm



Dimensions	
D	8mm +/-0.5mm
L	8mm +/-1mm
S	3.5mm +/-0.5mm
LL Negative	15mm MIN
LL Positive	19mm MIN
F	0.6mm +/-0.5mm

Packaging Specifications	
Packaging:	Bulk, Bag
Packaging Quantity:	500

General Information	
Dielectric:	Polymer Aluminum
Series:	A750
Description:	Single Ended, Polymer Aluminum
RoHS:	Yes
Lead:	Wire Leads

Specifications	
Capacitance:	560 uF
Capacitance Tolerance:	20%
Voltage DC:	10 VDC, 11.5 VDC (Surge)
Temperature Range:	-55/+105C
Rated Temperature:	105C
Life:	2000 Hrs (+/-20% Initial Capacitance, 1.5x DF MAX, Leakage Within Limit)
Dissipation Factor:	12% 120Hz 20C
Resistance:	16 mOhms (100kHz 20C)
Current:	4100 mAmps (100kHz 105C)
Leakage Current:	1120 uA (2min 20C)
Impedance Ratio at -25C:	1.25
Impedance Ratio at -55C:	1.25