

Ceramic, Commercial Grade, GoldMax, 0.01 uF, 1%, 100 V, COG, Lead Spacing = 5.08mm



#### Dimensions

L	7.11mm MAX
H	9.14mm MAX
T	4.07mm MAX
S	5.08mm NOM
LL	7mm MIN
F	0.51mm NOM

#### Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	250

#### General Information

Style:	Radial
Series:	GoldMax
Description:	GoldMax, Commercial Standard
RoHS:	Yes
Termination:	Tin
Failure Rate:	N/A

#### Specifications

Capacitance:	0.01 uF
Capacitance Tolerance:	1%
Voltage DC:	100 VDC
Temperature Range:	-55/+125C
Temperature Coefficient:	COG
Dissipation Factor:	0.1%
Aging Rate:	0% Loss/Decade Hour
Insulation Resistance:	100 GOhms
Dielectric Strength:	250 V