

Ceramic, Open Mode, AUTO-OpenMode-(CxxxxF-AUTO), 0.022 uF, 10%, 100 V, 0805, X7R, SMD, MLCC, Open Mode, Automotive Grade



| Dimensions | |
|------------|------------------|
| L | 2mm +/-0.2mm |
| W | 1.25mm +/-0.2mm |
| T | 1.25mm +/-0.15mm |
| S | 0.75mm MIN |
| B | 0.5mm +/-0.25mm |

| Packaging Specifications | |
|--------------------------|--------------------------|
| Packaging: | T&R, 180mm, Plastic Tape |
| Packaging Quantity: | 2500 |

| General Information | |
|---------------------|--------------------------------------------------------------------------|
| Style: | SMD Chip |
| Series: | AUTO-OpenMode-(CxxxxF-AUTO) |
| Chip Size: | 0805 |
| Description: | SMD, MLCC, Open Mode, Automotive Grade |
| Features: | Open Mode, Automotive Grade |
| RoHS: | Yes |
| Termination: | Tin |
| Marking: | No |
| Failure Rate: | N/A |
| Approvals: | AEC-Q200 |
| AEC-Q200: | Yes |
| Miscellaneous: | Note: Referee time for X7R dielectric for this part number is 1000 hours |

| Specifications | |
|----------------------------------|---------------------|
| Capacitance: | 0.022 uF |
| Capacitance Tolerance: | 10% |
| Voltage DC: | 100 VDC |
| Dielectric Withstanding Voltage: | 250 V |
| Temperature Range: | -55/+125C |
| Temperature Coefficient: | X7R |
| Dissipation Factor: | 2.5% |
| Aging Rate: | 3% Loss/Decade Hour |
| Insulation Resistance: | 4.545 GOhms |