

Flush-type connector - SACC-E-M12FSS-3P-M16/0,5 PE - 1411654

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Flush-type connector, Power, 3-position, SocketLink:M12, S power, Front mounting, M16 x 1.5, Individual wires, Cable length: 0.5 m

Why buy this product

- Compact power supply voltage connector
- For industrial infrastructure applications
- Protection against mismatching thanks to S-coding
- Pre-assembled with litz wires for immediate use
- Customer-specific assemblies and litz wire lengths available
- Sealed on the litz wire side for optimum leak-tightness
- For high transmission safety: shield connection to the housing with optional EMC nut



Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 1 STK |
| GTIN |  4 046356 937498 |
| GTIN | 4046356937498 |
| Weight per Piece (excluding packing) | 41.200 g |
| Custom tariff number | 85366990 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|-----------------|-------|
| Length of cable | 0.5 m |
|-----------------|-------|

Ambient conditions

| | |
|---------------------------------|-----------------------------------|
| Ambient temperature (operation) | -25 °C ... 105 °C (Plug / socket) |
|---------------------------------|-----------------------------------|

General

| | |
|------|--|
| Note | The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if |
|------|--|

Flush-type connector - SACC-E-M12FSS-3P-M16/0,5 PE - 1411654

Technical data

General

| | |
|-----------------------------|---|
| | there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration. |
| Rated current at 40°C | 16 A |
| Rated voltage | 630 V |
| Rated surge voltage | 2 kV |
| Number of positions | 3 |
| Insulation resistance | ≥ 100 MΩ |
| Coding | S power |
| Standards/regulations | M12 connector |
| Signal type/category | Power |
| Status display | No |
| Overvoltage category | III |
| Degree of pollution | 3 |
| Connection method | Individual wires |
| Insertion/withdrawal cycles | > 100 |
| Torque | 3 Nm ... 4 Nm (M12 connector) |
| Mounting type | Front mounting M16 x 1.5 |

Material

| | |
|--|---------------------------|
| Flammability rating according to UL 94 | V0 |
| Contact material | CuZn |
| Contact surface material | Au |
| Contact carrier material | PA |
| Material, knurls | CuZn alloy, nickel-plated |
| Sealing material | FKM |

Cable

| | |
|---------------------------------|--|
| Cable type | PP litz wire |
| Conductor cross section | 1.5 mm ² |
| AWG signal line | 16 |
| Wire colors | black 1, black 2, green/yellow |
| Material conductor insulation | PP |
| Conductor material | Bare Cu litz wires |
| Standards/specifications | M12 connector |
| Ambient temperature (operation) | -40 °C ... 105 °C (without mechanical actuation) |
| | -40 °C ... 90 °C (cable, fixed installation) |
| | -30 °C ... 90 °C (cable, flexible installation) |

Standards and Regulations

| | |
|--|---------------|
| Standard designation | M12 connector |
| Flammability rating according to UL 94 | V0 |

Environmental Product Compliance

Flush-type connector - SACC-E-M12FSS-3P-M16/0,5 PE - 1411654

Technical data

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | Environmentally Friendly Use Period = 50 |
| | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |


Drawings

Schematic diagram




Pin assignment: M12 socket, 3-pos., S-coded, view of socket side

Dimensional drawing




M12 flush-type socket

Circuit diagram



Contact assignment of the M12 socket

Diagram



Derating diagram

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 5.1 | 27143423 |
| eCl@ss 6.0 | 27143423 |
| eCl@ss 8.0 | 27440103 |
| eCl@ss 9.0 | 27440102 |

ETIM

| | |
|----------|----------|
| ETIM 4.0 | EC002061 |
| ETIM 5.0 | EC002061 |
| ETIM 6.0 | EC002061 |

UNSPSC

| | |
|-------------|----------|
| UNSPSC 13.2 | 39121413 |
|-------------|----------|

Flush-type connector - SACC-E-M12FSS-3P-M16/0,5 PE - 1411654

Approvals

Approvals

Approvals

UL Listed / cUL Listed / EAC / cULus Listed

Ex Approvals

Approval details

| | | | |
|--------------------------------|-------|---|---------------|
| UL Listed | | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm | FILE E 468743 |
| | | | |
| mm ² /AWG/kcmil | 16 | | |
| Nominal current I _N | 12 A | | |
| Nominal voltage U _N | 600 V | | |

| | | | |
|--------------------------------|-------|---|---------------|
| cUL Listed | | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm | FILE E 468743 |
| | | | |
| mm ² /AWG/kcmil | 16 | | |
| Nominal current I _N | 12 A | | |
| Nominal voltage U _N | 600 V | | |

| | | |
|-----|--|---------|
| EAC | | B.01742 |
|-----|--|---------|

| | |
|--------------|--|
| cULus Listed | |
|--------------|--|

Accessories

Accessories

Flat nut

Flush-type connector - SACC-E-M12FSS-3P-M16/0,5 PE - 1411654

Accessories

Flat nut - SACC-E-MU-M16 - 1504097



Flat nut with M16 thread

Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>