

Flush-type connector - SACC-MCI-MST-4CON/0,5 SCO - 1424130

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Assembled contact carrier and insulating body, T-coding, 4-pos., 0.5 m long litz wires

Why buy this product

- For compact devices: transmit high power in a confined space
- Convenient field assembly: device connectors for fast on-site mounting
- Customer-specific assemblies and litz wire lengths available
- Standard pin assignments for signal and power transmission with a uniform design-in design

Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 693332
GTIN	4046356693332
Weight per Piece (excluding packing)	36.100 g
Custom tariff number	85366990
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length of cable	0.5 m
-----------------	-------

Ambient conditions

Ambient temperature (operation)	-25 °C ... 85 °C
Degree of protection	IP67

General

Note	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using
------	---

Flush-type connector - SACC-MCI-MST-4CON/0,5 SCO - 1424130

Technical data

General

	a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
Rated current at 40°C	12 A
Rated voltage	63 V
Rated surge voltage	1.5 kV
Number of positions	4
Insulation resistance	≥ 100 MΩ
Coding	T power
Standards/regulations	M12 connector
Signal type/category	Power
Status display	No
Overvoltage category	III
Degree of pollution	3
Connection method	Individual wires
Torque	M12 connector
Mounting type	With flat nut

Material

Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA6

Cable

Cable type	PP litz wire
AWG signal line	16
Wire colors	Black, brown, blue, white
Conductor material	Bare Cu litz wires
Standards/specifications	M12 connector
Ambient temperature (operation)	-40 °C ... 90 °C (cable, fixed installation)

Standards and Regulations

Standard designation	M12 connector
----------------------	---------------


Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings


Flush-type connector - SACC-MCI-MST-4CON/0,5 SCO - 1424130

Schematic diagram



Pin assignment for M12 plug, 4-pos., T-coded, view of plug side

Circuit diagram



Contact assignment of the M12 plug

Classifications

eCl@ss

eCl@ss 4.0	27140815
eCl@ss 4.1	27140815
eCl@ss 5.0	27143423
eCl@ss 5.1	27143423
eCl@ss 6.0	27143423
eCl@ss 7.0	27449001
eCl@ss 8.0	27440103
eCl@ss 9.0	27440102

ETIM

ETIM 3.0	EC002061
ETIM 4.0	EC002062
ETIM 5.0	EC002061
ETIM 6.0	EC002061

UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	39121413

Approvals

Approvals

Approvals


EAC

Ex Approvals

Flush-type connector - SACC-MCI-MST-4CON/0,5 SCO - 1424130

Approvals

Approval details

EAC		B.01742
-----	---	---------

Accessories

Accessories

Panel mounting base

Flange - SACC-MSQ-P-M12MS-25-2,7 SCO - 1424131



Flange housing, 25 mm x 25 mm
