

# Control cabinet feed-through - VS-BH-M12FSX-10G-RJ45/90 - 1404548

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Control cabinet feed-through, M12, 8-pos., X-coded to RJ45 socket, socket input 90°, IP65/67

## Why buy this product

- Compact design
- 10 Gbps
- IP65/67
- UL



## Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 699419
GTIN	4046356699419
Weight per Piece (excluding packing)	36.000 g
Custom tariff number	85366990
Country of origin	Germany

## Technical data

### Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Ambient temperature (operation)	-25 °C ... 85 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C

### General data

Rated current at 40°C	0.5 A
Rated voltage	60 V

# Control cabinet feed-through - VS-BH-M12FSX-10G-RJ45/90 - 1404548

## Technical data

### General data

Number of positions	8
Signal type/category	Ethernet CAT6 <sub>A</sub> , 10 Gbps
Rated voltage (III/3)	50 V

### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

### Environmental Product Compliance


China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Drawings


Explosion drawing

Exploded drawing


Dimensional drawing



Dimensional drawing



Circuit diagram



Panel cutout

Circuit diagram

## Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27279220
eCl@ss 7.0	27440103

# Control cabinet feed-through - VS-BH-M12FSX-10G-RJ45/90 - 1404548

## Classifications

### eCl@ss

eCl@ss 8.0	27440312
eCl@ss 9.0	27440312

### ETIM

ETIM 4.0	EC001121
ETIM 5.0	EC002641
ETIM 6.0	EC002641

### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	39121419

## Approvals


### Approvals


#### Approvals

UL Listed / cUL Listed / EAC / cULus Listed

#### Ex Approvals

### Approval details


UL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> E335024-20140306
Nominal current IN	0.5 A	
Nominal voltage UN	60 V	

cUL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> E335024-20140306
Nominal current IN	0.5 A	
Nominal voltage UN	60 V	

# Control cabinet feed-through - VS-BH-M12FSX-10G-RJ45/90 - 1404548

## Approvals

EAC		B.01742
-----	---	---------

cULus Listed		
--------------	---	--