

AA ESD Cushion Grip Tweezers



5" 130 mm

Precision tips

ESD cushion grip handles

AA.SA.DR

Anti-Magnetic Anti-Acid Stainless Steel body with ESD rubber handles (DR)

General notes

- very soft and elastic, good tear resistance
- outstanding abrasion/wear resistance (improved life-time)
- good chemical resistance (oils, grease, fuels, acid, detergents and soaps); good hydrolytic resistance (hot water)
- electrically static dissipative, low surface resistivity (10^{12} ;- 10^{13} Ohm), ESD-safe material!
- typical applications include ESD-safe handles, floor and work surface mats

Mechanical properties

Hardness, Shore A	30	
Tensile modulus 100%	0.6 MPa	DIN 53504, 23°C
Tensile modulus 200%	1.1 MPa	DIN 53504, 23°C
Tensile modulus 300%	1.8 MPa	DIN 53504, 23°C
Tensile modulus 400%	2.6 MPa	DIN 53504, 23°C
Tensile strength, ultimate	10.4 MPa	DIN 53504, 23°C
Elongation at break	817.3%	DIN 53504, 23°C

Thermal properties

Continuous Use Temperature	100°C	20'000 h
Short Time Temperature	120°C	

Electrical properties

Surface resistivity:	10 ⁸ Ω; 10 ¹² Ω
----------------------	---------------------------------------

Other properties

Density	1.10 g/ccm	ISO 1183
---------	------------	----------

© IDEAL-TEK SA
Credits