


# ZC2JY81

limit switch lever ZC2JY - spring lever with thermoplastic end - -40..70°C



## Main

Range of product	OsiSense XC
Series name	Special format
Product or component type	Limit switch lever
Device short name	ZC2J
Product compatibility	XC2J
Associated head	ZC2JE01 ZC2JE02 ZC2JE03 ZC2JE04 ZC2JE05 ZC2JE06 ZC2JE07
Movement of operating head	Rotary
Type of operator	Spring rod lever spring return (with thermoplastic end)
Type of approach	Lateral approach

## Complementary

Switch actuation	By any moving part
Positive opening	Without

## Environment

Ambient air temperature for operation	-25...70 °C for standard environment -40...70 °C for low temperature
Ambient air temperature for storage	-40...70 °C for standard environment -40...70 °C for low temperature
Environmental characteristic	Low temperature Standard environment

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1012 - <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations