

KEMET Part Number: C1210C103J5GACTU
(C1210C103J5GAC7800)

Ceramic, Commercial-(CxxxxC), 0.01 uF, 5%, 50 V, 1210, COG, SMD, MLCC, Ultra-Stable, Low Loss, Class I



Dimensions

| | |
|----------|-----------------|
| L | 3.2mm +/-0.2mm |
| W | 2.5mm +/-0.2mm |
| T | 1.1mm +/-0.10mm |
| B | 0.5mm +/-0.25mm |

Packaging Specifications

| | |
|----------------------------|--------------------------|
| Packaging: | T&R, 180mm, Plastic Tape |
| Packaging Quantity: | 2500 |

General Information

| | |
|-----------------------|---|
| Style: | SMD Chip |
| Series: | Commercial-(CxxxxC) |
| Chip Size: | 1210 |
| Description: | SMD, MLCC, Ultra-Stable, Low Loss, Class I |
| Features: | Ultra-Stable, Low Loss, Class I |
| RoHS: | Yes |
| Termination: | Tin |
| Marking: | No |
| Failure Rate: | N/A |
| Miscellaneous: | Note: KEMET 50V rated parts may be operated at 63 Volts |

Specifications

| | |
|---|---------------------|
| Capacitance: | 0.01 uF |
| Capacitance Tolerance: | 5% |
| Voltage DC: | 50 VDC |
| Dielectric Withstanding Voltage: | 125 V |
| Temperature Range: | -55/+125C |
| Temperature Coefficient: | COG |
| Dissipation Factor: | 0.1% |
| Aging Rate: | 0% Loss/Decade Hour |
| Insulation Resistance: | 100 GOhms |