


Aluminum Electrolytic, 105C, ELG, 0.033 F, 20%, 25 V, -40/+105C

**Dimensions**

D	35mm +/-1mm
L	50mm +/-2mm
S	10mm +/-0.5mm
LL	5.8mm +/-1mm
F	2mm +/-0.1mm

**Packaging Specifications**

Packaging:	Bulk
------------	------

**General Information**

Dielectric:	Aluminum Electrolytic
Series:	ELG
Description:	Snap-In, Aluminum Electrolytic
RoHS:	Yes
Lead:	2 Pin

**Specifications**

Capacitance:	0.033 F
Capacitance Tolerance:	20%
Voltage DC:	25 VDC, 32 VDC (Surge)
Temperature Range:	-40/+105C
Rated Temperature:	105C
Life:	2000 Hrs
Dissipation Factor:	45% 120Hz 20C
Current:	5400 mAmps (120Hz)
Leakage Current:	3000 uAmps (5min 20C)