

Ceramic, AUTO-(CxxxxC-AUTO), 5600 pF, 5%, 200 V, 1206, COG, SMD, MLCC, Ultra-Stable, Low Loss, Automotive Grade



Dimensions

L	3.2mm +/-0.2mm
W	1.6mm +/-0.2mm
T	0.78mm +/-0.10mm
B	0.5mm +/-0.25mm

Packaging Specifications

Packaging:	T&R, 180mm, Plastic Tape
Packaging Quantity:	4000

General Information

Style:	SMD Chip
Series:	AUTO-(CxxxxC-AUTO)
Chip Size:	1206
Description:	SMD, MLCC, Ultra-Stable, Low Loss, Automotive Grade
Features:	Ultra-Stable, Low Loss, Automotive Grade
RoHS:	Yes
Termination:	Tin
Marking:	No
Failure Rate:	N/A
Approvals:	AEC-Q200
AEC-Q200:	Yes

Specifications

Capacitance:	5600 pF
Capacitance Tolerance:	5%
Voltage DC:	200 VDC
Dielectric Withstanding Voltage:	500 V
Temperature Range:	-55/+125C
Temperature Coefficient:	COG
Dissipation Factor:	0.1%
Aging Rate:	0% Loss/Decade Hour
Insulation Resistance:	100 GOhms