
KEMET Part Number: C340C224K2R5TA7303



Ceramic, GoldMax, 0.22 uF, 10%, 200 V, X7R, GoldMax, Commercial Standard, Lead Spacing = 5.08mm



Dimensions		
L	7.36mm MAX	
Н	10.16mm MAX	
Т	4.07mm MAX	
S	5.08mm +/-0.78mm	
LL	7mm MIN	
Н0	18mm MIN	
F	0.51mm +0.1/-0.025mm	

Packaging Specifications		
Packaging:	T&R, 305mm	
Packaging Quantity:	1000	

General Information		
Style:	Radial	
Series:	GoldMax	
Description:	GoldMax, Commercial Standard	
RoHS:	Yes	
Termination:	Tin	
Failure Rate:	N/A	
Halogen Free:	Yes	

Specifications		
Capacitance:	0.22 uF	
Capacitance Tolerance:	10%	
Voltage DC:	200 VDC	
Dielectric Withstanding Voltage:	500 V	
Temperature Range:	-55/+125C	
Temperature Coefficient:	X7R	
Dissipation Factor:	2.5% 25C	
Aging Rate:	3% Loss/Decade Hour	
Insulation Resistance:	4.55 GOhms	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

