


**KEMET Part Number: LDEIB2100KA0N00**  
(DEIB2100KA0N00)

Film, Metallized PEN Stacked, Commercial Grade, LDE, 0.01 uF, 10%, 250 V, 120 V, 125C, 1210, 2.1mm



**Dimensions**

Chip Size	1210
L	3.3mm +0.3/-0.1mm
W	2.5mm +/-0.3mm
T	2.1mm MAX
B	0.5mm +0.5/-0.3mm

**Packaging Specifications**

Packaging:	T&R
Packaging Quantity:	2250

**General Information**

Dielectric:	Metallized PEN Stacked
Style:	SMD Chip
Series:	LDE
RoHS:	Yes
Approvals:	AEC-Q200
AEC-Q200:	Yes

**Specifications**

Capacitance:	0.01 uF
Capacitance Tolerance:	10%
Voltage DC:	250 VDC
Voltage AC:	120 V
Temperature Range:	-55/+125C
Rated Temperature:	125C
Dissipation Factor:	0.8% 1kHz
Insulation Resistance:	1 GOhms
Max dVdt:	100 V