


Aluminum Electrolytic, 105C, PEG130, 2000 uF, -10/+30%, 40 V, -40/+105C



Note: '()' correspond to the letters used in the product bulletin

Dimensions

D	20mm +/-0.5mm
L	29mm +/-1mm
L1	35mm MIN
LL Negative	40mm +/-2mm
LL Positive	40mm +/-2mm
F	1mm +/-0.03mm

Packaging Specifications

Weight:	13 g
Packaging:	Bulk
Packaging Quantity:	150

General Information

Dielectric:	Aluminum Electrolytic
Style:	Axial
Series:	PEG130
Description:	Long Life Axial Aluminum Electrolytic
Features:	Long Life
RoHS:	Yes
Lead:	Wire Leads
Notes:	L1 is KEMET's recommendation for minimum distance between symmetrical Lead bend. Available only for Customer specific part numbers. Lead bend dimensions must be specified and confirmed per article.

Specifications

Capacitance:	2000 uF
Capacitance Tolerance:	-10/+30%
Voltage DC:	40 VDC
Temperature Range:	-40/+105C
Rated Temperature:	105C
Life:	37000 Hrs
Resistance:	59 mOhms (100Hz 20C), 32 mOhms (100kHz 20C), 17 mOhms (5-100kHz 105C)
Current:	1.44 Amps (100Hz 105C), 8.8 Amps (5kHz 60C), 7.2 Amps (5kHz 80C), 4 Amps (5kHz 100C), 2.6 Amps (>=5kHz 105C)
Leakage Current:	244 uA (5min 20C)