


Aluminum Electrolytic, 85C, PEH200, 0.022 F, 20%, 100 V, -40/+85C



Dimensions

| | |
|----|---------------|
| D | 66.6mm +/-1mm |
| L | 106mm +/-1mm |
| T | 3.8mm NOM |
| S | 28.5mm |
| F | 15mm +/-0.5mm |
| DT | 15mm NOM |
| G | 13mm NOM |
| LT | 113mm +/-1mm |
| Z | 13mm NOM |

Packaging Specifications

| | |
|---------------------|-------|
| Weight: | 415 g |
| Sleeving: | Yes |
| Packaging: | Bulk |
| Packaging Quantity: | 12 |

General Information

| | |
|--------------|---|
| Dielectric: | Aluminum Electrolytic |
| Series: | PEH200 |
| Description: | Screw Terminal, Aluminum Electrolytic |
| RoHS: | Yes |
| Notes: | Dimensions D And L Include Sleeving. M5 |

Specifications

| | |
|------------------------|---|
| Capacitance: | 0.022 F |
| Capacitance Tolerance: | 20% |
| Voltage DC: | 100 VDC |
| Temperature Range: | -40/+85C |
| Rated Temperature: | 85C |
| Life: | 15000 Hrs (Rated Voltage And Ripple Current At 85C) |
| Resistance: | 15 mOhms (100Hz 20C), 13 mOhms (100kHz 20C) |
| Current: | 19.3 Amps (100Hz 85C), 38.7 Amps (10kHz 50C), 30.1 Amps (10kHz 40C) |
| Leakage Current: | 10600 uAmps (5min 20C) |
| Inductance: | 16 nH (ESL) |