

**KEMET Part Number: PHE850EA4330MA02R17**  
(F850AH332M300A)



Film, Metallized Polypropylene, Safety, PHE850/F850, 3300 pF, 20%, 1,250 V, 300 V, 110C, Lead Spacing = 10mm



General Information	
<b>Dielectric:</b>	Metallized Polypropylene
<b>Style:</b>	Radial
<b>Series:</b>	PHE850/F850
<b>Features:</b>	Pulse
<b>RoHS:</b>	Yes
<b>Lead:</b>	Wire Leads
<b>Approvals:</b>	ENEC, UL, cUL
<b>Miscellaneous:</b>	Not For New Design, Please Check Possible Alternative Parts (AltPart)

Dimensions	
<b>L</b>	13mm MAX
<b>H</b>	10.5mm MAX
<b>T</b>	4.5mm MAX
<b>S</b>	10mm +/-0.4mm
<b>LL</b>	17mm NOM
<b>F</b>	0.6mm NOM

Specifications	
<b>Capacitance:</b>	3300 pF
<b>Capacitance Tolerance:</b>	20%
<b>Voltage DC:</b>	1250 VDC
<b>Voltage AC:</b>	300 VAC
<b>Temperature Range:</b>	-55/+110C
<b>Rated Temperature:</b>	110C
<b>Dissipation Factor:</b>	0.15% 1kHz, 0.2% 10kHz, 0.6% 100kHz
<b>Insulation Resistance:</b>	30 GOhms
<b>Max dVdt:</b>	100 V
<b>Safety Class:</b>	Y2

Packaging Specifications	
<b>Packaging:</b>	Bulk
<b>Packaging Quantity:</b>	1000

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.



© 2006 - 2017 IntelliData.net