


Aluminum Electrolytic, 85C, ALT22, 0.015 F, 20%, 63 V, -40/+85C



General Information	
Dielectric:	Aluminum Electrolytic
Series:	ALT22
Description:	Solder Tag, Aluminum Electrolytic
Features:	Solder Tag
RoHS:	Yes
Lead:	2 Flying Leads Solder Tags
Notes:	Dimensions D And L Include Slewing

Dimensions	
D	40mm +/-1mm
L	75mm +/-2mm
S	10mm +/-0.1mm
LL	10mm +/-0.5mm

Specifications	
Capacitance:	0.015 F
Capacitance Tolerance:	20%
Voltage DC:	63 VDC, 72.45 VDC (Surge)
Temperature Range:	-40/+85C
Rated Temperature:	85C
Life:	26000 Hrs
Leakage Current:	5670 uAmps (5min 20C)

Packaging Specifications	
Weight:	125 g
Slewing:	Yes
Packaging:	Bulk

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.