

Film, Metallized Polypropylene, Commercial Grade, R75, 0.1 uF, 5%, 1,600 V, 85C, Lead Spacing = 27.5mm



**Dimensions**

L	32mm +0.3mm
H	20mm +0.1mm
T	11mm +0.2mm
S	27.5mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm

**Packaging Specifications**

Packaging:	Bulk
Packaging Quantity:	336

**General Information**

Dielectric:	Metallized Polypropylene
Style:	Radial
Series:	R75
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
Miscellaneous:	Above 85C DC And AC Voltage Derating Is 1.25%/C

**Specifications**

Capacitance:	0.1 uF
Capacitance Tolerance:	5%
Voltage DC:	1600 VDC
Voltage AC:	650 VAC
Temperature Range:	-55/+105C
Rated Temperature:	85C
Dissipation Factor:	0.04% 1kHz, 0.06% 10kHz, 0.25% 100kHz
Insulation Resistance:	100 GOhms
Max dVdt:	1,500 V
Inductance:	18 nH